


NO	DESCRIPTION	DATE
①	USE STAINLESS STEEL INSTEAD OF BRASS	05.15.95
②	FLAT 9.5X2 → FLATS 8.0	12.15.98
③	BACKGROUND FORMAT UPDATED	05.02.02
④	BACKGROUND FORMAT UPDATED	07.21.09'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

7	INSULATION II	TEFLON	1	NONE
6	CENTER CONTACT	BRASS	1	GOLD
5	BODY	BRASS	1	NICKEL 100μ" MIN.
4	INSULATION I	TEFLON	1	NONE
3	WASHER	STAINLESS STEEL	1	NONE
2	GASKET	SILICONE	1	RED
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by _____ DATE: _____

DESCRIPTION		FME JACK - SMA PLUG						
製圖	DRAWN	TOLERANCE	品名	23-18 T.G.N	日期	DATE	版次	REV.
	Yoko		TITLE	\ROHS COMPLIANT <50Ω	07.13.92'		A-4	
檢圖	CHECK	.XX	單位	UNIT	DWG.NO.	23-0050		
	Jacky	±0.1	mm(in)	SCALE				
認定	APPROVAL	.XXX	比例	SCALE				
	Lewis	ANGLE ±5°	4:1					

佳楠精密電子股份有限公司
CHIN NAN PRECISION ELECTRONICS CO.,LTD.