


NO	DESCRIPTION	DATE
①	REDUCE SPRING FROM 2 PCS TO 1 PC	06.06.97
②	DEL REF. BACKGROUND FORMAT UPDATED	07.20.09
③	MODIFICATION CENTER CONTACT ⑨	01.12.10



### 1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz  
1.2 NOMINAL IMPEDANCE: 50 OHM

### 2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604  
2.2 CENTER CONTACT: BRASS PER JIS-C3604  
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

### 3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

### 4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -20° C TO +80° C

9	CENTER CONTACT	BRASS	1	GOLD
8	BODY	BRASS	1	NICKEL 100 μ" MIN.
7	INSULATION II	TEFLON	1	NONE
6	WASHER	BRASS	1	NICKEL
5	SPRING	SK-5	1	NICKEL
4	WASHER	BRASS	1	NICKEL
3	GASKET	RUBBER	1	RED
2	INSULATION I	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100 μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by \_\_\_\_\_

DATE: \_\_\_\_\_

DESCRIPTION		FME PLUG - BNC PLUG						
製圖	DRAWN	TOLERANCE	品名	23-11 T.G.N	日期	DATE	版次	REV.
	Yoko							
檢圖	CHECK	單位	UNIT	DWG.NO.	23-0043	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
	Jacky							
認定	APPROVAL	比例	SCALE					
	Lewis							