


NO	DESCRIPTION	DATE
△	BRASS → STAINLESS STEEL	05.15.95'
△	MODIFICATION FOR CENTER CONTACT	07.24.02'
△	BACKGROUND FORMAT UPDATED	02.02.09'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

7	BODY	BRASS	1	NICKEL 100μ" MIN.
6	INSULATION	TEFLON	1	NONE
5	CENTER CONTACT	BRASS	1	GOLD
4	INSULATION	TEFLON	1	NONE
3	WASHER	STAINLESS STEEL	1	NONE
2	GASKET	SILICONE	1	RED
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____ DATE: _____

DESCRIPTION		FME PLUG-SMA PLUG							
製圖	DRAWN	TOLERANCE		品名	23-14 T.G.N	日期	DATE	版次	REV.
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT <50Ω>		04.29.93		A-3
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	23-0046		
	Jacky	.XXX	±0.05	mm(in)	SCALE		佳楠精密電子股份有限公司		
認定	APPROVAL	ANGLE	±5°	比例	SCALE	CHIN NAN PRECISION ELECTRONICS CO.,LTD.			
	Lewis				4:1				