



Specification For SBC75-16

DIMENSIONS



A: 6.4 Max	mm
B: 1.3 Max	mm
C: 2.5±0.3	mm
D: 7.5 Max	mm
E: 9.0 Max	mm
F: 5.0±0.5	mm
G: 6.4 Max	mm
H: φ 0.6±0.1	mm
I: 1.25±0.5	mm
J: 3.5±1.0	mm

SCHEMATIC



ELECTRICAL SPECIFICATIONS

TEST INSTRUMENTS

L : CH1062A LCZ METER (or equivalent)

RDC : CHROMA MODEL 16502 MILLIOHM METER (or equivalent)

- 1 Temperature rise +40°C Max.
- 2 Ambient temperature +60°C Max.
- 3 Operate temperature range -25°C ~ +70°C
(Including self temp. rise)
- 4 Storage temperature range -25°C ~ +70°C

Inductance L(μH)	Test Frequency	Resistance RDC(mΩ)Max.	Insulation Resistance (MΩ) Min.	Rated Voltage Vdc(V) Max.	Rated current Max (mA)
16±50%	1kHz/0.25V	35	10	50	500