


## Glass Passivated Single-Phase Bridge Rectifier



Case Style WOG

| MAJOR RATINGS AND CHARACTERISTICS |                |
|-----------------------------------|----------------|
| $I_{F(AV)}$                       | 1.5 A          |
| $V_{RRM}$                         | 50 V to 1000 V |
| $I_{FSM}$                         | 50 A           |
| $I_R$                             | 5 $\mu$ A      |
| $V_F$                             | 1.0 V          |
| $T_j \text{ max.}$                | 150 °C         |

### FEATURES

- UL Recognition, file number E54214
- Ideal for printed circuit boards
- Typical  $I_R$  less than 0.1  $\mu$ A
- High case dielectric strength
- High surge current capability
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



### TYPICAL APPLICATIONS

General purpose use in ac-to-dc bridge full wave rectification for Power Supply, Adapter, Charger, Lighting Ballaster on Consumers and Home Appliances applications.

### MECHANICAL DATA

**Case:** WOG

Epoxy meets UL 94V-0 flammability rating

**Terminals:** Silver plated leads, solderable per J-STD-002B and JESD22-B102D

E4 suffix for commercial grade

**Polarity:** As marked on body

| MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)                                   |                |               |      |      |      |      |      |      |                    |
|---|----------------|---------------|------|------|------|------|------|------|--------------------|
| PARAMETER   | SYMBOL         | W005G         | W01G | W02G | W04G | W06G | W08G | W10G | UNIT               |
| Maximum repetitive peak reverse voltage   | $V_{RRM}$      | 50            | 100  | 200  | 400  | 600  | 800  | 1000 | V                  |
| Maximum RMS voltage   | $V_{RMS}$      | 35            | 70   | 140  | 280  | 420  | 560  | 700  | V                  |
| Maximum DC blocking voltage   | $V_{DC}$       | 50            | 100  | 200  | 400  | 600  | 800  | 1000 | V                  |
| Maximum average forward rectified current at 0.375" (9.5 mm) lead length at $T_A = 25$ °C | $I_{F(AV)}$    | 1.5           |      |      |      |      |      |      | A                  |
| Peak forward surge current single sine-wave superimposed on rated load                    | $I_{FSM}$      | 50            |      |      |      |      |      |      | A                  |
| Rating for fusing ( $t < 8.3$ ms)   | $I^2t$         | 10            |      |      |      |      |      |      | A <sup>2</sup> sec |
| Operating junction and storage temperature range  | $T_J, T_{STG}$ | - 55 to + 150 |      |      |      |      |      |      | °C                 |

| ELECTRICAL CHARACTERISTICS ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted) |   |        |            |      |      |      |      |      |      |               |
|---|---|--------|------------|------|------|------|------|------|------|---------------|
| PARAMETER   | TEST CONDITIONS   | SYMBOL | W005G      | W01G | W02G | W04G | W06G | W08G | W10G | UNIT          |
| Maximum instantaneous forward voltage drop per diode                                  | at 1.0 A  | $V_F$  | 1.0        |      |      |      |      |      |      | V             |
| Maximum DC reverse current at rated DC blocking voltage per diode                     | $T_A = 25\text{ }^\circ\text{C}$<br>$T_A = 125\text{ }^\circ\text{C}$ | $I_R$  | 5.0<br>500 |      |      |      |      |      |      | $\mu\text{A}$ |
| Typical junction capacitance per diode  | at 4.0 V, 1 MHz   | $C_J$  | 14         |      |      |      |      |      |      | pF            |

| THERMAL CHARACTERISTICS ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted) |                                    |          |      |      |      |      |      |      |                    |  |
|--|------------------------------------|----------|------|------|------|------|------|------|--------------------|--|
| PARAMETER  | SYMBOL                             | W005G    | W01G | W02G | W04G | W06G | W08G | W10G | UNIT               |  |
| Typical thermal resistance <sup>(1)</sup>  | $R_{\theta JA}$<br>$R_{\theta JL}$ | 36<br>11 |      |      |      |      |      |      | $^\circ\text{C/W}$ |  |

**Note:**

(1) Thermal resistance from junction to ambient and from junction to lead at 0.375" (9.5 mm) lead length P.C.B. mounting. P.C.B size 0.22 x 0.22" (5.5 x 5.5 mm)

| ORDERING INFORMATION |                 |                        |               |               |
|----------------------|-----------------|------------------------|---------------|---------------|
| PREFERRED P/N        | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE |
| W06G-E4/51           | 1.12            | 51                     | 100           | Plastic Bag   |

### RATINGS AND CHARACTERISTICS CURVES

( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)




Figure 1. Derating Curve Output Rectified Current




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current Per Diode




Figure 3. Typical Forward Characteristics Per Diode




Figure 5. Typical Junction Capacitance Per Diode




Figure 4. Typical Reverse Leakage Characteristics Per Diode





Figure 6. Typical Transient Thermal Impedance

### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





## Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.