# Type: M3PRT/2 & M3PRT/2-4W


## Phase Failure, Phase Sequence and Under Voltage plus Time Delay

- 35mm DIN rail housing
- Microprocessor controlled with internal monitoring (self-checking)
- Monitors own supply and detects an Under voltage condition on one or more phases
- M3PRT/2 measures phase to phase voltage and M3PRT/2-4W measures phase to neutral voltage
- Detects incorrect phase sequence, phase loss and neutral loss (4-wire only)
- Adjustment for under voltage trip level
- Adjustment for time delay (from an under voltage condition)
- 1 x DPDT relay output 8A
- Intelligent LED indication for supply and relay status





**FUNCTION DIAGRAM** 



### INSTALLATION AND SETTING

BEFORE INSTALLATION, ISOLATE THE SUPPLY.



Installation work must be carried

Connect the unit as required. The diagram below shows a typical installation, whereby the supply to the load is being monitored by the relay. If a fault should occur, the contactor is de-energised removing the 3-phase supply to the load. The contactor only re-energises after the fault has cleared.

#### Applying power

- Set the "trip level" and the "time delay" to minimum.
- Apply power and the green "supply on" and red "relay" LED's will illuminate, the relay will energise and contacts 15 and 18 / 25 and 28 will close. Refer to troubleshooting table if the unit fails to operate correctly

#### Setting the unit

- Accurate setting can be achieved by adjusting the "trip level" until the unit trips (relay de-energises) then by decreasing the "trip level" setting until the relay re-energises. By close setting of the "trip level", the unit will also detect a phase loss even with a large percentage of re-generative voltage.
- In order to set the unit as previously described but without causing disruption to the equipment being controlled/monitored, set the "time delay" to maximum. It will now be possible to establish the trip point when the red "relay" LED starts to flash. Decrease the trip level setting to stop the LED flashing. (Note: If the time delay is allowed to expire, the output relay will de-energise).
- If large supply variations are anticipated, the "trip level" should be set further from the nominal
- Set the "time delay" as required. (Note that the delay is only effective should the supply drop below the set "trip level". However, if during an under voltage condition the supply drops below the 2under voltage trip level, any set time delay is automatically cancelled and the relay de-energises).

Troubleshooting. The table below shows the status of the unit during a fault condition.

Supply fault	Green LED	Red LED	Relay
Phase or Neutral (4-wire only) missing	Off	Off	De-energised
Phases reversed (no delay)	Flashing	Off	De-energised
Under Voltage condition (during timing)	On	Flashing	Energised for set delay (t)
Under Voltage condition (after timing)	On	Off	De-energised
Phase below 70% of Un (fixed under trip level [2])	On	Off	De-energised
Phase below 50% of Un	Off	Off	De-energised

## **TECHNICAL SPECIFICATION**

Supply / monitoring voltage U\*:

M3PRT/2 (L1, L2, L3) 77- 143V AC 161 - 300V AC

Over voltage cat. III

Under [2] fixed ±2%:

44.5 - 82.5V AC 93 - 173V AC

M3PRT/2-4W (L1, L2, L3, N)

Supply / monitoring

Under (adjustable):

83 - 138V

voltage when ordering

280 - 520V AC 48 - 63Hz

161 - 300V AC \*Please state

Isolation: Rated impulse withstand voltage: Power consumption:

Frequency range

4kV (1.2 / 50µS) IEC 60664

L1: 20VA (3-wire), 13VA (4-wire)

L2: 0.2VA (3-wire), 0.1VA (4-wire) L3: 20VA (3-wire), 0.1VA (4-wire)

Trip levels: Voltage range

77 - 143V AC (3-wire) 161 - 300V AC (3-wire) 280 - 520V AC (3-wire) 44.5 - 82.5V AC (4-wire)

161V 173 - 288V 300 - 500V 48 - 79V 44 5V 93 - 173V AC (4-wire) 100 - 166V 93V 161V 173 - 288V

161 - 300V AC (4-wire) ± 0.5% @ constant conditions Repeat accuracy: Hysteresis: ≈ 2% of trip level (factory set) Response time: ≈ 50 mS

Time delay (t): 0.2 - 10 sec (+ 5%) Note: actual delay (t) = adjustable delay + response time

Delay from  $\approx 100 \text{ mS (worst case} = \text{tr x 2)}$ 

phase/neutral loss (tr):

Power on delay (Td): ≈ 1sec. (worst case = Td x 2)

-20 to +60°C Ambient temp: Relative humidity + 95% Output: DPDT relay (15, 16, 18 / 25, 26, 28)

Output rating: AC1 250V 8A (2000VA) 250V 3A AC15 25V 8A (200W) Electrical life: ≥ 150,000 ops at rated load 2kV AC (rms) IEC 60947-1

Dielectric voltage: Rated impluse withstand voltage:

4kV (1.2 / 50µS) IEC 60664

Housing: Orange flame retardant UL94 VO Weight:

On to 35mm symmetric DIN rail to BS5584:1978 Mounting option:

(EN50 002, DIN 46277-3) Or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on


the rear of the unit  $\leq$  2 x 2.5mm<sup>2</sup> solid or stranded


Terminal conductor size: Conforms to IEC. CE and Compliant. Approvals

Ontions

- 1. For other supply/monitoring voltages, please consult the sales office.
- 2. For alternative time delays or trip levels, please consult the sales office.

## **CONNECTION DIAGRAM**





Broyce Control Ltd., Pool Street, Wolverhampton, West Midlands WV2 4HN. England

M3PRT2-2-A

Telephone: +44 (0) 1902 773746 Facsimile: +44 (0) 1902 420639 Email: sales@broycecontrol.com Web: http://www.broycecontrol.com The information provided in this literature is believed to be accurate (subject to change without prior notice); however, use of such information shall be entirely at the user's own risk.