



# Static Sensitive Brushes

2060-2064

## Introduction

---

These dissipative brushes have a surface resistivity of  $10^6 - 10^8$  ohms, which makes them an excellent addition to any ESD program. Each brush is made with a revolutionary, non-sloughing, static dissipative material to prevent any static generation. For your safety, please use these brushes with a wrist strap or other mechanism to provide a good path to ground.

## Chemical Components

---

This product does not contain any hazardous ingredients as per OSHA 29 CFR 1910.1200 Subpt.(z).

## Environmental Policy

---

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

## Packaging and Availability

---

Static Sensitive Brushes are available in the following sizes:

2060-1	2063-1
2061-1	2064-1
2062-1	

## Resources

---

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

### North America

Tech Spray L.P.  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

### Europe

Techspray International  
UNIT 4, 44/46 Bunyan Road, Kempston  
Bedford MK42 8HL United Kingdom  
+44 (0) 1234 855443  
email: [tseurope@techspray.com](mailto:tseurope@techspray.com)

### Countries Outside US

Call to locate a distributor  
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.  
P.O. Box 949  
Amarillo, TX 79105  
[www.techspray.com](http://www.techspray.com)

[English MSDS](#)  
[French MSDS](#)  
[German MSDS](#)  
[Italian MSDS](#)  
[Spanish MSDS](#)



	2060	2061	2062	2063	2064
Bristle Length	1 3/16"	1 3/16"	1/2"	1/4"	1/8"
Bristle Width	1/8"	3/8"	3/8"	3/16"	1/16"
Bristle Trim	7/16"	7/16"	A-1/4" B-3/16"	A-1/4" B-3/16"	1/8"
Bristle Material	Proprietary Static Dissipative Material	Proprietary Static Dissipative Material	Proprietary Static Dissipative Material	Proprietary Static Dissipative Material	Proprietary Static Dissipative Material
Bristle Retention	Hand Laced	Hand Laced	Machine Stamped	Machine Stamped	Machine Stamped
Handle Material	Aluminum	Aluminum	Zinc Plated Steel	Stainless Steel	Stainless Steel
Handle Length	6 7/16"	6 7/16"	4 1/2"	4 1/2"	3 1/2"
Bulk Pack	6	6	6	6	6