

SAFETY DATA SHEET (EC 1907/2006)**Microbond Flux Paste 5070**

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	1 / 7

**1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING****Product information**

Trade name : Microbond Flux Paste 5070

Company : Umicore AG & Co. KG
Postfach 1351
Rodenbacher Chaussee 4
D-63403 Hanau

Telephone : +49 (0)6181 59-4887
Telefax : +49 (0)6181 59-4150
Email address : msds@eu.umicore.com
Emergency telephone number : +32 (0)3 213-1570

Use of the Substance / Preparation : For industrial use

2. HAZARDS IDENTIFICATION**Additional safety information for humans and the environment**

Irritating to skin.
Risk of serious damage to eyes.
May cause sensitization by skin contact.
Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

3. COMPOSITION/INFORMATION ON INGREDIENTS**Chemical nature**

preparation

Information on ingredients / Hazardous components

- **Amines,coco alkyl,ethoxylated** >= 5% - < 10%
CAS-No. 61791-14-8
C, N
R22, R34, R50, R53
- **Malonic acid** >= 3% - <= 7%
CAS-No. 141-82-2
Xn
R22, R36
EC-No. 205-503-0
- **2-ethylhexane-1,3-diol** >= 15% - <= 40%
CAS-No. 94-96-2
Xi; R41
EC-No. 202-377-9
- **Rosin** >= 40% - <= 70%
CAS-No. 8050-09-7
Xi; R43
EC-No. 232-475-7
- **Polyethylene glycol butyl ether**
CAS-No. 9004-77-7

SAFETY DATA SHEET (EC 1907/2006)

Microbond Flux Paste 5070

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	2 / 7



Xi
R36

- **Castor oil**

CAS-No. 8001-79-4 EC-No. 232-293-8

See chapter 16 for text of risk phrases

4. FIRST AID MEASURES

General advice

Remove victims from hazardous area.

Inhalation

Move victims into fresh air.

Skin contact

After contact with skin, wash immediately with plenty of soap and water.
Take off all contaminated clothing immediately.

Eye contact

Rinse immediately with plenty of water for 15 minutes and seek advice of an eye specialist.

Ingestion

Have patient drink plenty of water in small sips.
Do not induce vomiting.
Aspiration hazard!
In case of discomfort: Supply with medical care.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Water, water vapour, extinguishing powder, extinguishing foam, alcohol stable extinguishing foam, carbon dioxide (CO₂)

Specific hazards during fire fighting

Formation of flammable or explosive vapour/air mixtures possible.
In the event of fire and/or explosion do not breathe fumes.
Danger of explosion with fire.

Further information

Water used to extinguish fire should not enter drainage systems, soil, or stretches of water. Ensure there are sufficient retaining facilities for water used to extinguish fire. Contaminated fire-extinguishing water must be disposed of in accordance with the regulations issued by the appropriate local authorities. Retention of fire-extinguishing water in Germany: see FireExtinguishing Water Retention Directive "LoeRueRL":

6. ACCIDENTAL RELEASE MEASURES

Personal precautions

Do not breathe vapours/dust.
Avoid contact with skin and eyes.
Keep people away from and upwind of spill/leak.
Wear personal protective equipment; see section 8.

Environmental precautions

Prevent penetration into soil, stretches of water and drainage systems.

SAFETY DATA SHEET (EC 1907/2006)

Microbond Flux Paste 5070

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	3 / 7



Methods for cleaning up

Absorb with liquid-binding material, e. g.: sand diatomaceous earth inert absorbent.

Additional advice

Remove all sources of ignition.

7. HANDLING AND STORAGE

Handling

Safe handling advice

The product should only be handled by trained personnel.
Ensure suitable suction/aeration at the work place and with operational machinery.
Keep out of the reach of children.
Do not breathe vapours/dust.
Avoid contact with skin and eyes.

Storage

Requirements for storage areas and containers

Fumes may be released in closed storage rooms or during processing.
Keep container dry and tightly sealed - even empties.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Components with workplace control parameters

• Rosin

CAS-No.	8050-09-7	EC-No.	232-475-7
Control parameters	0.05 mg/m ³		Time Weighted Average (TWA):(EH40 WEL)
type of exposition	Fume.		
Control parameters	0.15 mg/m ³		Short Term Exposure Limit (STEL):(EH40 WEL)
type of exposition	Fume.		

Other information

None known.

Personal protective equipment

Respiratory protection

In case of dusts/vapours/aerosols being formed or if the limit values like TLV are exceeded:
Suitable filter: A-P2, code colour brown-white

Hand protection

Wear suitable gloves.

Glove material	nitrile rubber
Material thickness	0.35 mm
Break through time	> 480 min

The rupture time and material thickness data are guideline values! Exact rupture time / material thickness data can be obtained from the protective glove manufacturer.

The information is based on our own tests, references from the literature and information from glove manufacturers, or derived by analogy with similar materials.

Selection of protective gloves to meet the requirements of specific workplaces.

Suitability for specific workplaces should be clarified with protective glove manufacturers.

SAFETY DATA SHEET (EC 1907/2006)**Microbond Flux Paste 5070**

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	4 / 7

**Eye protection**

goggles

When handling larger quantities: protective screen

Skin and body protection

Use suitable skin protective agents before handling product. Cleanse and apply cream to skin after work. Preventive skin protection recommended.

Wear suitable protective clothing.

Hygiene measures

Wash face and/or hands before break and end of work.

9. PHYSICAL AND CHEMICAL PROPERTIES**Appearance**

Form	pasty
Colour	colourless
Odour	solvent
physical state	liquid

Safety data

pH	not applicable
Boiling point/range	243 °C
Flash point	125 °C
Method:	DIN 51758
Flammability	Flammable.
Ignition temperature	215 °C
Method:	DIN 51 794
Lower explosion limit	0.7 %(V)
Upper explosion limit	5.3 %(V)
Density	0.9 g/cm ³
Water solubility	partly soluble
Partition coefficient (n-octanol/water)	not determined
Viscosity, dynamic	not determined

10. STABILITY AND REACTIVITY

Conditions to avoid

When heated above flashpoint and/or with spraying or atomization, a flammable mixture may form with air.

SAFETY DATA SHEET (EC 1907/2006)**Microbond Flux Paste 5070**

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	5 / 7

**11. TOXICOLOGICAL INFORMATION**

No results of animal experiments with the product available.

12. ECOLOGICAL INFORMATION**Elimination information (persistence and degradability)****Behaviour in environmental compartments****Ecotoxicity effects**

Ecotoxicological tests with this preparation are not available.

13. DISPOSAL CONSIDERATIONS**Product**

Dispose of as waste requiring special control in accordance with the legal regulations issued by the appropriate local and national authorities.

If recycling is not practicable, dispose of in compliance with local regulations.

No waste key number as per the European Waste Types List can be assigned to this product, since such classification is based on the (as yet undetermined) use to which the product is put by the consumer.

The waste key number must be determined as per the European Waste Types List (decision on EU Waste Types List 2000/532/EC) in cooperation with the disposal firm / producing firm / official authority.

14. TRANSPORT INFORMATION**Land transport ADR/RID/GGVSE (Germany)**

Class	8
ADR/RID-Labels	8
UN-No	2735
Packaging group	II
orange warning plate	80 / 2735
Description of the goods (Technical name)	POLYAMINES, LIQUID, CORROSIVE, N.O.S. (coconut fatty acid, ethoxylated)

Sea transport IMDG-Code/GGVSee

Class	8
UN-No	2735
Packaging group	II
EmS	F-A, S-B
Proper technical name (Proper shipping name)	POLYAMINES, LIQUID, CORROSIVE, N.O.S. (coconut fatty acid, ethoxylated)

Air transport ICAO-TI/IATA-DGR

Class	8
UN-No	2735
Packaging group	II
Proper technical name (Proper shipping name)	Polyamines, liquid, corrosive, n.o.s. (coconut fatty acid, ethoxylated)

SAFETY DATA SHEET (EC 1907/2006)**Microbond Flux Paste 5070**

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	6 / 7

**Inland waterway transport ADN/ADNR/GGVBinSch (Germany)**

Class	8
ADR/RID-Labels	8
UN-No / Substance number	2735
Packaging group	II
Description of the goods (Technical name)	POLYAMINES, LIQUID, CORROSIVE, N.O.S. (coconut fatty acid, ethoxylated)

Loading instructions/Remarks

IATA_C	ERG-Code 8L
IATA_P	ERG-Code 8L
IMDG	Keep separate from acids.

Transport/further information

Keep separate from foodstuffs, luxury foods, feedstuffs

15. REGULATORY INFORMATION**Labelling according to EC Directives****hazard-defining component(s)**

- Amines,coco alkyl,ethoxylated
- 2-ethylhexane-1,3-diol
- Rosin

Symbol(s)	Xi N	Irritant Dangerous for the environment
R-phrase(s)	R38 R41 R43 R51/53	Irritating to skin. Risk of serious damage to eyes. May cause sensitization by skin contact. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
S-phrase(s)	S 2 S23 S24/25 S26 S36/37/39 S61	Keep out of the reach of children. Do not breathe gas/fumes/vapour/spray. Avoid contact with skin and eyes. In case of contact with eyes, rinse immediately with plenty of water and seek medical advice. Wear suitable protective clothing, gloves and eye/face protection. Avoid release to the environment. Refer to special instructions/safety data sheets.

SAFETY DATA SHEET (EC 1907/2006)**Microbond Flux Paste 5070**

Material no.		Version	4.4 / GB
Specification	135920	Revision date	16.08.2007
VA-Nr		Print Date	07.08.2008
		Page	7 / 7

**National legislation****16. OTHER INFORMATION****Risk phrase (R phrase) texts**• **Amines,coco alkyl,ethoxylated**

R22	Harmful if swallowed.
R34	Causes burns.
R50	Very toxic to aquatic organisms.
R53	May cause long-term adverse effects in the aquatic environment.

• **Malonic acid**

R22	Harmful if swallowed.
R36	Irritating to eyes.

• **2-ethylhexane-1,3-diol**

R41	Risk of serious damage to eyes.
-----	---------------------------------

• **Rosin**

R43	May cause sensitization by skin contact.
-----	--

• **Polyethylene glycol butyl ether**

R36	Irritating to eyes.
-----	---------------------

Further information

Changes since the last version are highlighted in the margin. This version replaces all previous versions.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.