




## Surface Mount Schottky Barrier Rectifier



DO-213AB

### FEATURES

- MELF Schottky rectifier
- Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- Low forward voltage drop
- High surge capability
- Meets MSL level 1, per J-STD-020C, LF max peak of 250 °C
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



### MAJOR RATINGS AND CHARACTERISTICS

$I_{F(AV)}$	1.0 A
$V_{RRM}$	20 V to 60 V
$I_{FSM}$	30 A
$V_F$	0.50 V, 0.70 V
$T_j \text{ max.}$	125 °C, 150 °C

### TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, free-wheeling, dc-to-dc converters, and polarity protection applications

### MECHANICAL DATA

**Case:** DO-213AB

Epoxy meets UL 94V-0 flammability rating

**Terminals:** Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

E3 suffix for commercial grade, HE3 suffix for high reliability grade (AEC Q101 qualified)

**Polarity:** Two bands indicate cathode end 1st band denotes device type 2nd band denotes voltage type

### MAXIMUM RATINGS ( $T_A = 25\text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
Denotes Schottky devices: 1st band is orange		<b>SGL41-20</b>	<b>SGL41-30</b>	<b>SGL41-40</b>	<b>SGL41-50</b>	<b>SGL41-60</b>	
Polarity color bands (2nd band) voltage type		Gray	Red	Orange	Yellow	Green	
Maximum repetitive peak reverse voltage	$V_{RRM}$	20	30	40	50	60	V
Maximum RMS voltage	$V_{RMS}$	14	21	28	35	42	V
Maximum DC blocking voltage	$V_{DC}$	20	30	40	50	60	V
Maximum average forward rectified current (see Fig.)	$I_{F(AV)}$	1.0					A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	$I_{FSM}$	30					A
Voltage rate of change (rated $V_R$ )	dv/dt	10000					V/ $\mu$ s
Operating junction temperature range	$T_J$	- 55 to + 125			- 55 to + 150		°C
Storage temperature range	$T_{STG}$	- 55 to + 150					°C

ELECTRICAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER	TEST CONDITIONS	SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
			SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Maximum instantaneous forward voltage <sup>(1)</sup>	at 1.0 A	V <sub>F</sub>	0.50			0.70		V
Maximum reverse current at rated DC blocking voltage <sup>(1)</sup>	T <sub>A</sub> = 25 °C T <sub>A</sub> = 100 °C	I <sub>R</sub>	0.5					mA
			10		5.0			
Typical junction capacitance	at 4.0 V, 1.0 MHz	C <sub>J</sub>	110			80		pF

**Note:**

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)							
PARAMETER	SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Maximum thermal resistance <sup>(1)</sup>	R <sub>θJA</sub>	75					°C/W
	R <sub>θJT</sub>	30					

**Note:**

(1) Thermal resistance junction to terminal, 0.24 x 0.24" (6.0 x 6.0 mm) copper pads to each terminal

ORDERING INFORMATION				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SGL41-40-E3/96	0.114	96	1500	7" Diameter Plastic Tape & Reel
GL41-40-E3/97	0.114	97	5000	13" Diameter Plastic Tape & Reel
BYM13-40-E3/96	0.114	96	1500	7" Diameter Plastic Tape & Reel
BYM13-40-E3/97	0.114	97	5000	13" Diameter Plastic Tape & Reel

## RATINGS AND CHARACTERISTICS CURVES

(T<sub>A</sub> = 25 °C unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current



# BYM13-20 thru BYM13-60, SGL41-20 thru SGL41-60

Vishay General Semiconductor




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance





Figure 4. Typical Reverse Characteristics

## PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

### DO-213AB



1st band denotes type and positive end (cathode)



## Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.