


Machine Tube Luminaire




AWDCE 118

connected load	230 V; 50 Hz
fitted with	1 x compact fluorescent lamp TC-DEL 18 W neutral white 4000 K
work equipment	electronic ballast
mains lead	appr. 3 m; special plug
luminaire body material	borosilicate glass
weight (net)	approx. 0,8 kg
fastening	thread M40 x 1.5
light distribution	direct
system of protection	IP 67
class of protection	II
total length	255 mm
light output	144 mm
article no.	112154001



E_{min}: 92 lx
E_m: 289 lx
E_{max}: 598 lx



measuring conditions: 50

