

## Magnifier Luminaire



RLL 122 T

connected load  
fitted with

work equipment  
mains lead  
luminaire body  
material

tubular sections  
material

weight (net)

fastening  
technology

usage

lamp cover

balance of articulation joints

class of protection

colour luminaire body

colour of tubular sections

lens; dimensions

lens; diopters

add-on lens

article no.

230 V; 50 Hz

1 x fluorescent lamp T29-R 22 W  
neutral white

conventional ballast

approx. 1.9 m; three-prong plug (BS1363A)

plastic

plastic

approx. 3,1 kg

table clamp (accessory)~wall bracket (accessory)

switchable

switch

polycarbonate; white opal

spring

II

light grey


light grey

Ø 120 mm


4

Ø 30 mm / total 12 Diopters

111851023



Emin: 838 lx  
Em: 2162 lx  
Emax: 3255 lx



measuring conditions: d=15cm

