## **2.19** AZM 190 range





#### **Features**

- Thermoplastic enclosure
- Manual / Emergency release
- Long life
- Actuation on de-energisation or energisation
- Slim design, particularly suitable for fitting on hinged doors, aluminium profiles and fencing
- Actuating head can be turned in 4 steps of 90°
- Sealing mechanism to prevent the ingress of dirt
- 2 cable entries
- Wiring compartment
- Holding force 1,500 N


# Voltage variants


24 VDC 24 VAC 48 VAC 110 VAC


110 VAC 230 VAC

Always state required supply voltage

when ordering








#### **Approvals**



# Manual release



- For manual release using triangular key
- For maintenance, setting-up, etc.


# Emergency release



- In case of danger
- Fitting only within the protected area

#### **2.19** AZM 190 range





#### Notes

Circuit diagrams show de-energised condition with actuator inserted (0 in switch travel diagram). Actuators must be ordered separately. A selection of suitable actuators can be found in 2.20.

Interlocks with actuation on energisation may only be used in special cases after a thorough evaluation of the accident risk, since the guarding device can immediately be opened on failure of the electrical power supply or when the main switch is opened.

Info

• LED version on enquiry


#### 2.20 Actuators



9


## Straight actuator AZM 190-B1

- Particularly suitable for sliding doors
- Compensation for tolerances by means of rubber buffers
- Play of key in interlocked condition approx. 5 mm
- On hinged guards, minimum actuating radius at 90° to the plane of the actuator 175 mm, minimum actuating radius in line with the plane of the actuator 650 mm






• The axis of the hinge should be 7.5 mm above the top edge of the solenoid interlock and in the same plane




### Actuator with front fixing AZM 190-B5

- Particularly suitable for front mounting e.g. on hinged guards
- Play of key in interlocked condition approx. 5 mm
- On hinged guards, minimum actuating radius at 90° to the plane of the actuator 250 mm, minimum actuating radius in line with the plane of the actuator 650 mm






• The axis of the hinge should be 15.5 mm above the top edge of the solenoid interlock and in the same plane




# Adjustable actuator AZM 190-B3/2x15

- For very small actuating radii at 90° to or in line with the plane of the actuator
- $\bullet$  Play of key in interlocked condition approx. 5 mm
- On hinged guards, minimum actuating radius at 90° to the plane of the actuator 275 mm, minimum actuating radius in line with the plane of the actuator 350 mm





• The axis of the hinge should be 20 mm above the top edge of the solenoid interlock and in the same plane



#### 2.20 Actuators




## Adjustable actuator AZM 190-B3/15

- With actuator preset at 15° for small actuating radii
- Play of key in interlocked condition approx. 5 mm
- On hinged guards, minimum actuating radius at 90° to the plane of the actuator 150 mm



• The axis of the hinge should be 20 mm above the top edge of the solenoid interlock and in the same plane




## Adjustable actuator AZM 190-B3/7.5

- With actuator preset at 7.5°
- Play of key in interlocked condition approx. 5 mm
- On hinged guards, minimum actuating radius at 90° to the plane of the actuator 175 mm



• The axis of the hinge should be 20 mm above the top edge of the solenoid interlock and in the same plane




#### 2.21 Accessories




### Mounting plate MP 190

• For simple mounting of an AZM 190 on profile systems



## Additional entry ZPG 190

• Cover with Pg cable entry




# Triangular key M3

- For manual release
- Part number:

Straight: Triangular key M3 (included in delivery)

With lever: Triangular key M3-a



## 2.27 Technical data



	AZM 170-F05 AZM 170i-F05	AZM 170-Z05 AZM 170i-Z05	AZM 190
Standards:	IEC/EN 60947-5-1/DIN VDE0660-200; EN 1088; BG-GS-ET-19		
Enclosure material:	Glass-fibre reinforced thermoplastic, self-extinguishing		Glass-fibre reinforced
			thermoplastic
Actuator and latching bolt:	Stainless steel 1.4301		Zinc-plated metal / aluminium
Protection class:	IP 65		IP 67
	to IEC/EN 60529/DIN VDE 0470-1		
Contact material:	Silver		
Contact type:	Changeover with double break Zb,		Changeover with
	with galvanically separated contact bridges		double break Zb
			with galvanically iso-
			lated moving contacts
Switching system:	⊖ IEC 60947-5-1; <sup>®</sup> BG-GS-ET-19; slow action, NC contacts with positive break		
Termination:	Removable terminal block with cage clamps		Screw terminals for max. 2.5 mm <sup>2</sup>
	max. 1.5 mm <sup>2</sup>		cables (including conductor ferrules)
Rated impulse			
withstand voltage U <sub>imp</sub> :	4 kV		2.5 kV
Rated insulation voltage Ui:	250 V		400 V
Thermal test current Ith:	10 A		
Utilisation category:	AC-15		AC-15; DC-13
Rated operating			
current/voltage I <sub>e</sub> /U <sub>e</sub> :	4 A/230 V		8 A/230 V,
			5 A/24 VDC
Max. fuse rating:	6 A gL/gG D-fuse		10 A gL/gG D-fuse
Positive break travel:	11 mm		2 x 3.5 mm
Positive break force:	6 N for each NC		20 N
	contact fitted		
Solenoid duty rating:	Continuous operation		
Rated control voltage U <sub>S</sub> :	24 VAC/DC		24 VDC; 48 VAC;
	or 110 VAC/DC, 50/60 Hz		110 VAC; 230 VAC
	or 230 VAC/DC, 50/60 Hz		
Consumption:	Max. 10 W		Max. 8.5 W
Ambient temperature:	0 °C + 55 °C		0 °C + 50 °C
Mechanical life:	> 1 million operations		2 million operations
Holding force F <sub>max.</sub> :	1,000 N		1,500 N
Holding force of	.,===		
integral ball latch:	_		
Latching force:	- 30 N		
C C	0011		

C€