

LIGHTS
2000
Sabrelite™ Zone 1

Save page as PDF



SabreLite™ 2000 Zone 1 Flashlight



Same features as the SabreLite™ 2000 with static-dissipation materials body. SabreLite™ 2000Z1 is ATEX certified safe for use in hazardous Zone 1 (Category 2) locations, and is perfect for professionals who work in areas with high risk of explosion such as chemical, pharmaceutical, power, oil and gas, and fire rescue.

SabreLite™ 2000 Zone 1 Flashlight SPECIFICATIONS

Length	Light Source	Tested Lumen Value	Tested Lux Value (@ 1 meter)
19.8 cm (7.79")	Xenon	33.00	10,000
Batteries	Battery Burn Time	Battery Pack Charging Time	
3 C Alkaline (Not included)	5 hrs.	N/A	
Voltage	Weight w/Batteries	Weight w/o Batteries	
4.5	0.36 kg (12.8 oz.)	0.15 kg (5.31 oz.)	

Materials

Body	Lens	Shroud	Switch Type
EXL	Polycarbonate	Xenoy	Twist On/Off Lens Shroud
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
ABS	Stainless Steel	Ethylene Propylene	N/A

Configuration

Cat. #	Description
2000Z1	SabreLite™ 2000Z1

SabreLite™ 2000 Zone 1 Flashlight Accessories

Cat. #	Description
2004Z1	SabreLite^a 2000 Zone 1 Lamp Module

Approvals

CE Ex - II 2G Ex e ib IIC T4 (Energizer), 150°C (Panasonic Plus, Duracell)
 Certificate: ITS09ATEX26181X