

TL7700A Series

SUPPLY VOLTAGE SUPERVISORS

- POWER-ON RESET GENERATOR
- AUTOMATIC RESET GENERATION AFTER VOLTAGE DROP
- WIDE SUPPLY VOLTAGE RANGE ... 3V TO 18V
- PRECISION VOLTAGE SENSOR
- TEMPERATURE-COMPENSATED VOLTAGE REFERENCE
- TRUE AND COMPLEMENT RESET OUTPUTS
- EXTERNALLY ADJUSTABLE PULSE WIDTH

DESCRIPTION

The TL7700A series are monolithic supply voltage supervisor IC's specifically designed for use as reset controllers in microcomputer and microprocessor systems. During power-up the device tests the supply voltage and keeps the RESET and RESET outputs active (high and low, respectively) as long as the supply voltage has not reached its nominal voltage value. Taking RESIN low has the same effect. To ensure that the microcomputer system has reset. the TL7700A then initiates an internal time count that delays the return of the reset outputs to their inactive states. Since the time delay for most microcomputers and microprocessors is in the order of several machine cycles, the device internal time delay is determined by an external capacitor connected to the C_T input (pin 3).

$t_{po} = 1.3 \times 10^4 \times C_T$


Where : C_T is in farads (F) and t_{po} in seconds (s). In addition, when the supply voltage drops below the nominal value, the outputs will be active until the supply voltage returns to the nominal value. An external capacitor (typically 0.1 μ F) must be connected to the REF output (pin 1) to reduce the influence of fast transients in the supply voltage.


The TL7700AI series is characterized for operation from – 25° C to 85° C; the TL7700AC series is characterized from 0° C to 70° C.

ORDERING NUMBERS

Temperature Range	Minidip	S08	
0 to 70°C	TL77XXACP	TL77XXACD	
-25 to 85°C	TL77XXAIP	TL77XXAID	

PIN CONNECTION (top view)





Symbol	Parameter	Test Conditions (1)	Min.	Тур.	Max.	Unit	
V _{OH}	High-level Output Voltage at RESET	I _{OH} = -16mA	V _s - 1.5			V	
V _{OL}	Low-Level Output Voltage at RESET		I _{OL} = 16mA		0.4		V
V _{ref}	Reference Voltage		$T_{amb} = 25^{\circ}C$	2.48	2.53	2.58	V
VT	Threshold Voltage at SENSE Input	TL7702A TL7705A	$V_s = 3.6V \text{ to } 18V$ $T_{amb} = 25^{\circ}C$	2.48 4.5	2.53 4.55	2.58 4.6	V
VT	Threshold Voltage at SENSE Inpu	TL7702A TL7705A	$V_{s} = 3.6V$ to 18V	2.45 4.45	2.53 4.55	2.58 4.6	V
V_{T+}, V_{T-}	Hysteresis (2) at SENSE Input	TL7702A TL7705A	$V_s = 3.6V \text{ to } 18V$ $T_{amb} = 25^{\circ}C$		10 15		mV
lı	Input Current at RESIN Input				20 -100		μΑ
h	Input Current at SENSE Input	TL7702A	$V_{ref} < V_i < V_s$ - 1.5V		0.5	2	μΑ
I _{OH}	High-level Output Current at RESET		V _O = 18V		50		μΑ
lol	Low-level Output Current at RESET		$V_0 = 0V$		-50		μΑ
ls	Supply Current		All Inputs and out. open		1.8	3.3	mA

ELECTRICAL CHARACTERISTICS these specifications unless otherwise specified, apply for : $T_{amb} = -25$ to $85^{\circ}C$ (TLXXAI), $T_{amb} = 0$ to $70^{\circ}C$ (TL77XXAC)


Notes: 1. All characteristics are measured with C = 0.1μF from Pin 1 to GND, and with C = 0.1μF from Pin 3 to GND.
2. Hysteresis is the difference between the positive going input threshold voltage. V_{T+}, and the negative going input threshold voltage, V_{T-}.

SWITCHING CHARACTERISTICS

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
t _{pi}	Pulse Width at SENSE Input	$ \begin{array}{l} V_{ih} = V_{ityp} + 0.04 \ x \ V_i \\ V_{iL} = V_{ityp} - 0.04 \ x \ V_i \end{array} $	0.9			μs
t _{pi}	Pulse Width at RESIN Input		0.4			μs
t _{po}	Pulse Width at Output	$C_T = 0.1 \mu F$	0.65	1.3	2.6	ms
t _{pdHL}	Propagation Delay Time from RESIN to RESET	$C_L = 100 \text{pF}, \text{ V}_\text{s} = 5 \text{V}, \text{ R}_\text{L} = 4.7 \text{k} \Omega$			1	μs
t _{r/f}	Rise/Falltime at RESET and RESET	C_L = 10pF, V_s = 5V, R_L = 4.7k Ω			1	μs


TL7700A Series

Figure 1 : Reset Controller for μP




57

DIM.	mm			inch			
Diwi.	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
А			1.75			0.069	
a1	0.1		0.25	0.004		0.010	
a2			1.65			0.065	
a3	0.65		0.85	0.026		0.033	
b	0.35		0.48	0.014		0.019	
b1	0.19		0.25	0.007		0.010	
С	0.25		0.5	0.010		0.020	
c1			45° ((typ.)			
D (1)	4.8		5.0	0.189		0.197	
E	5.8		6.2	0.228		0.244	
е		1.27			0.050		
e3		3.81			0.150		
F (1)	3.8		4.0	0.15		0.157	
L	0.4		1.27	0.016		0.050	
М			0.6			0.024	
S	8° (max.)						




(1) D and F do not include mold flash or protrusions. Mold flash or potrusions shall not exceed 0.15mm (.006inch).




57

TL7700A Series

DIM.	mm			inch			
2	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
А		3.32			0.131		
a1	0.51			0.020			
В	1.15		1.65	0.045		0.065	
b	0.356		0.55	0.014		0.022	
b1	0.204		0.304	0.008		0.012	
D			10.92			0.430	
E	7.95		9.75	0.313		0.384	
е		2.54			0.100		
e3		7.62			0.300		
e4		7.62			0.300		
F			6.6			0.260	
I			5.08			0.200	
L	3.18		3.81	0.125		0.150	
Z			1.52			0.060	





Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics © 2000 STMicroelectronics – Printed in Italy – All Rights Reserved STMicroelectronics GROUP OF COMPANIES Australia - Brazil - China - Finland - France - Germany - Hong Kong - India - Italy - Japan - Malaysia - Malta - Morocco -Singapore - Spain - Sweden - Switzerland - United Kingdom - U.S.A. http://www.st.com

57