




NOTES:

1. MATERIALS AND FINISHES (PLATING THICKNESS IN MICRO-INCHES):
 BODY - BRASS, NICKEL PLATING
 CONTACT - BRASS, GOLD PLATING
 INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
 A. IMPEDANCE: 75 OHM
 B. FREQUENCY RANGE: DC-3 GHz
 C. RETURN LOSS: BETTER THAN
 35 dB @ 0-1 GHz;
 30 dB @ 1-2 GHz;
 26 dB @ 2-3 GHz
- D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
 A. DURABILITY: 500 CYCLES MIN.
 B. TEMPERATURE RANGE: -10° TO +85°
4. CRIMPED FERRULE
 HEX CRIMP SIZE .197"
5. CRIMPED CONTACT PIN
 SQ. CRIMP SIZE .042"
6. SMITH CHART TEST REPORT MUST BE ATTACHED WITH EACH SHIPMENT

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	21-Mar-08		RL
AI	ADDED CUSTOMER NO.	11-May-09		SCOTT



CUSTOMER OUTLINE DRAWING
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the finishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN R. LUO	DATE 11-May-09	TITLE BNC CRIMP PLUG (FOR DRAKA 0.6/2.8 AF CABLE) HDTV		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com
	REFERENCE	ENGINEER HARRY	DATE 21-Mar-08			
	FINISH	APPROVED SCOTT	DATE 11-May-09	ITEM NO. 011121AMBAINA7F		
		CAD FILE 1:\BNC\B1121A8-011-NT3G-75	SCALE: 4.0:1.0	SHEET 2 OF 2	PART NO.	