






LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
B		REVISED PER ECO 08-009474	7/22/2008	DW	JL		



- 1 POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-0 RATED, COLOR:NATURAL
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 ZINC PER QQ-Z-363.
- 4 PHOSPHOR BRONZE PER QQ-B-750.
- 5 BRASS PER ASTM-B-453.
- 6 NICKEL PLATE PER QQ-N-290, 3.81 μm [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204, 0.76 μm [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 408-2769.



5226978-3	
5226978-1	
CONTACT PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J. ALCORTA - 25APR2005		Tyco Electronics Corporation	
DIMENSIONS: INCHES		DOCK 5 J. HAVENER - 25APR2005		Harrisburg, Pa 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT - 25APR2005		NAME	
0 PLC ± -	1 PLC ± -	PRODUCT SPEC		JACK, RIGHT ANGLE, 50 OHM, PCB, SERIES BNC	
2 PLC ± 0.20 [.008]	3 PLC ± -	APPLICATION SPEC		108-12078	
4 PLC ± -	ANGLES ± -	SIZE		CAGE CODE	
MATERIAL SEE NOTES 1-5		FINISH SEE NOTES 6-9		DRAWING NO	
WEIGHT		A1 00779		C=5226978	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1	
				REV B	