


230°C Pocket Infrared Thermometer



Product Description



This pocket size and easy-to-use infrared thermometer is ideal for precise non-contact measurement of surface temperatures. Suitable for monitoring appliances, heating, ventilation & air conditioning systems, food preparation and storage temperatures.

- -35° to $230^{\circ}\text{C} \times 0.1^{\circ}$
- User selectable $^{\circ}\text{C}/^{\circ}\text{F}$
- Hold within 2 feet of the area to be measured, push the button, read the display
- Distance to spot size ratio is 1 to 1 at the focal point
- Fixed emissivity at 0.95
- Response time less than 1 second
- Large 12mm LCD Display with function indicators
- Automatic Data Hold
- Set Min/Max and Lock
- Auto Power Off
- Low Battery indication
- Impact-resistant ABS case
- Supplied with carry case, wrist strap & lithium battery

Technical Specification

Range -35° to $+230^{\circ}\text{C}$ (-31° to $+446^{\circ}\text{F}$)

Resolution $0.1^{\circ}\text{C}/^{\circ}\text{F}$

Accuracy $\pm 2\%$ of reading or $\pm 2^{\circ}\text{C}$ (-10° to $+230^{\circ}\text{C}$), $\pm 4^{\circ}\text{C}$ (-10° to -35°C)

Power 1 x 3V Lithium Button Cell Battery (**ACR-2032**)

Dimensions 75 x 40 x 20mm

Weight 33g