

# YAGEO CORPORATION

**Lead-Free & RoHs Compliance!!**

## SPECIFICATION FOR APPROVAL

CUSTOMER : \_\_\_\_\_  
CUSTOMER P/N : \_\_\_\_\_  
OUR DWG No : \_\_\_\_\_  
QUANTITY : \_\_\_\_\_ Pcs.      DATE : \_\_\_\_\_  
ITEM :                      **SBK160808T-102Y-N**

SPECIFICATION ACCEPTED BY:	
COMPONENT ENGINEER	
ELECTRICAL ENGINEER	
MECHANICAL ENGINEER	
APPROVED	
REJECTED	


DRAWN BY Sally Lo	CHECKED BY Ling Wen	APPROVED BY Eric Chung
----------------------	------------------------	---------------------------

# YAGEO CORPORATION

## SBK160808T Series Specification

**1 Scope:** This specification applies to MUTILAYER FERRITE CHIP BEADS

**2 Part Numbering: Product Identification**



**3 Rating:**

**Operating Temperature:** -55℃~125℃

**Storage Temperature:** Under 25℃, Humidity 40%~65%

**4 Marking:**

No Marking


**5 Standard Testing Condition**

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35℃)	20±2℃
Humidity	Ordinary Humidity(25 to 85% RH)	60 to 70 % RH

# YAGEO CORPORATION

## SBK160808T Series Specification

### 6 Configuration and Dimensions:



Dimensions in mm

TYPE	SB 160808
A	1.6±0.15
B	0.8±0.15
C	0.8±0.15
D	0.3±0.20

### 7 ELECTRICAL CHARACTERISTICS :

Part No.	Impedance ( $\Omega$ )	Test Freq. (MHZ)	RDC ( $\Omega$ )Max.	Rated Current (mA)Max.
SBK160808T-060□-N	6	100 MHZ,200 mV	0.05	500
SBK160808T-070□-N	7	100 MHZ,200 mV	0.05	500
SBK160808T-100□-N	10	100 MHZ,200 mV	0.05	500
SBK160808T-110□-N	11	100 MHZ,200 mV	0.05	500
SBK160808T-150□-N	15	100 MHZ,200 mV	0.08	500
SBK160808T-170□-N	17	100 MHZ,200 mV	0.08	500
SBK160808T-190□-N	19	100 MHZ,200 mV	0.08	500
SBK160808T-200□-N	20	100 MHZ,200 mV	0.1	400
SBK160808T-220□-N	22	100 MHZ,200 mV	0.1	400
SBK160808T-250□-N	25	100 MHZ,200 mV	0.1	400
SBK160808T-260□-N	26	100 MHZ,200 mV	0.1	400
SBK160808T-300□-N	30	100 MHZ,200 mV	0.1	400
SBK160808T-310□-N	31	100 MHZ,200 mV	0.1	400
SBK160808T-320□-N	32	100 MHZ,200 mV	0.1	400
SBK160808T-330□-N	33	100 MHZ,200 mV	0.1	400
SBK160808T-400□-N	40	100 MHZ,200 mV	0.1	400
SBK160808T-470□-N	47	100 MHZ,200 mV	0.1	400
SBK160808T-500□-N	50	100 MHZ,200 mV	0.1	400
SBK160808T-520□-N	52	100 MHZ,200 mV	0.1	400
SBK160808T-550□-N	55	100 MHZ,200 mV	0.1	400
SBK160808T-560□-N	56	100 MHZ,200 mV	0.1	400
SBK160808T-600□-N	60	100 MHZ,200 mV	0.1	400
SBK160808T-680□-N	68	100 MHZ,200 mV	0.15	400
SBK160808T-700□-N	70	100 MHZ,200 mV	0.15	400
SBK160808T-750□-N	75	100 MHZ,200 mV	0.15	400

NOTE: □-tolerance Y=±25% / T=±30%

1.Operating temperature range - 5 5℃ ~ 1 2 5℃

2.Rate Current : Applied the current to coils, the temperature rise shall not be more than 30℃

"-N" FOR COMPLETELY LEAD FREE TYPE(INCLUDING FERRITE BODY & SOLDER)

# YAGEO CORPORATION

## SBK160808T Series Specification


Part No.	Impedance ( $\Omega$ )	Test Freq. (MHZ)	RDC ( $\Omega$ )Max.	Rated Current (mA)Max.
SBK160808T-80□-N	80	100 MHZ,200 mV	0.15	400
SBK160808T-90□-N	90	100 MHZ,200 mV	0.2	400
SBK160808T-101□-N	100	100 MHZ,200 mV	0.2	400
SBK160808T-121□-N	120	100 MHZ,200 mV	0.25	400
SBK160808T-141□-N	140	100 MHZ,200 mV	0.25	300
SBK160808T-151□-N	150	100 MHZ,200 mV	0.25	300
SBK160808T-181□-N	180	100 MHZ,200 mV	0.3	300
SBK160808T-201□-N	200	100 MHZ,200 mV	0.3	300
SBK160808T-221□-N	220	100 MHZ,200 mV	0.3	300
SBK160808T-241□-N	240	100 MHZ,200 mV	0.4	300
SBK160808T-301□-N	300	100 MHZ,200 mV	0.4	300
SBK160808T-331□-N	330	100 MHZ,200 mV	0.5	300
SBK160808T-401□-N	400	100 MHZ,200 mV	0.5	300
SBK160808T-421□-N	420	100 MHZ,200 mV	0.5	300
SBK160808T-451□-N	450	100 MHZ,200 mV	0.5	300
SBK160808T-471□-N	470	100 MHZ,200 mV	0.5	300
SBK160808T-501□-N	500	100 MHZ,200 mV	0.5	300
SBK160808T-601□-N	600	100 MHZ,200 mV	0.5	300
SBK160808T-751□-N	750	100 MHZ,200 mV	0.6	300
SBK160808T-801□-N	800	100 MHZ,200 mV	0.6	300
SBK160808T-102□-N	1000	100 MHZ,200 mV	0.6	300
SBK160808T-122□-N	1200	100 MHZ,200 mV	0.6	300
SBK160808T-152□-N	1500	100 MHZ,200 mV	0.6	300
SBK160808T-172□-N	1700	100 MHZ,200 mV	0.8	200
SBK160808T-202□-N	2000	100 MHZ,200 mV	0.8	200
SBK160808T-222□-N	2200	100 MHZ,200 mV	0.8	200
SBK160808T-252□-N	2500	100 MHZ,200 mV	0.8	200
SBK160808T-272□-N	2700	100 MHZ,200 mV	0.8	200

# YAGEO CORPORATION

## SBK160808T Series Specification

### 8 SBK160808T Series

#### 8.1 Construction:



#### 8.2 Material List:


NO	PART	MATERIAL
1	Ferrite Substance	NiO-CuO-ZnO-Ferrite
2	Silver electrode	Ag
3	Silver electrode	Ag
4	Cu plating	Cu
5	Ni plating	Ni
6	Sn plating	Sn

# YAGEO CORPORATION

## SBK160808T Series Specification

### 9 Reliability Of Ferrite Multilayer Chip Bead

#### 1-1. Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Flexure Strength	The forces applied on the right conditions must not damage the terminal electrode and the ferrite	Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 30sec *For 100505, substrate dimension is 100x40x0.8mm
1-1-2	Vibration		Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-3	Resistance to Soldering Heat	Appearance: No damage More than 75% of the terminal electrode should be covered with solder. Impedance : within $\pm 30\%$ of initial value	Pre-heating: 150°C, 1min Solder Composition: Sn/Pb = 63/37 Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 260 $\pm$ 5°C Immersion Time: 10 $\pm$ 1sec
1-1-4	Solder ability	The electrodes shall be at least 90% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Pb = 63/37 Solder Temperature: 220 $\pm$ 5°C Solder Composition: Sn/Ag3.0/Cu0.5(Pb-Free) Solder Temperature: 245 $\pm$ 5°C (Pb-Free) Immersion Time: 4 $\pm$ 1sec
1-1-5	Terminal Strength Test	100505 series : $\geq 0.2$ kg 160808 series : $\geq 0.5$ kg 201209 series : $\geq 1.0$ kg other series : $\geq 2.0$ kg BAY/BAQ321609 series : $\geq 1.5$ kg (Push)	Test device shall be soldered on the substrate 

#### 1-2. Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Cycle	Appearance: No damage Impedance: within $\pm 30\%$ of initial value	One cycle:															
			<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 5%;">Step</th> <th style="width: 75%;">Temperature (°C)</th> <th style="width: 20%;">Time (min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>2</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> <tr> <td>3</td> <td>125<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>4</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> </tbody> </table>	Step	Temperature (°C)	Time (min)	1	-55 $\pm$ 3	30	2	25 $\pm$ 2	3	3	125 $\pm$ 3	30	4	25 $\pm$ 2	3
			Step	Temperature (°C)	Time (min)													
			1	-55 $\pm$ 3	30													
			2	25 $\pm$ 2	3													
3	125 $\pm$ 3	30																
4	25 $\pm$ 2	3																
Total: 100cycles																		
Measured after exposure in the room condition for 24hrs																		
1-2-2	Humidity Resistance	Temperature: 40 $\pm$ 2°C Relative Humidity: 90 ~ 95% / Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-3	High Temperature Resistance	Temperature: 125 $\pm$ 3°C / Relative Humidity: 0% Applied Current: Rated Current / Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-4	Low Temperature Resistance	Temperature: -55 $\pm$ 3°C Relative Humidity: 0% / Time: 1000hrs Measured after exposure in the room condition for 24hrs																

# YAGEO CORPORATION

## SBK160808T Series Specification



Lead-Free(LF) 標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升温區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T. ~ 150°C	150°C ~ 200°C	217°C	260±5°C	Peak Temp. ~ 150°C
標準時間 Time spec.	—	60 ~ 180 sec	60 ~ 150sec	20 ~ 40 sec	—
實際時間 Time result	—	75 ~ 100 sec	90 ~ 120sec	20 ~ 35 sec	—

NOTE :

1. Re-flow possible times : within 2 times
2. Nitrogen adopted is recommended while in re-flow

# YAGEO CORPORATION

## SBK160808T Series Specification

### 10 TEST DATA FOR PREPRODUCTION SAMPLES

QF-1419

#### DESCRIPTION: SBK160808T-102Y-N

MEAS. Item	Z ( $\Omega$ )	RDC ( $\Omega$ )	A m/m	B m/m	C m/m	D m/m					
Spec Customer	1000 $\pm$ 25%										
Suggest		0.60+0	1.6 $\pm$ 0.15	0.8 $\pm$ 0.15	0.8 $\pm$ 0.15	0.3 $\pm$ 0.20					
Test Freq. (MHz)	200mV 100										
1	921	0.158	1.65	0.88	0.86	0.35					
2	951	0.158	1.61	0.88	0.84	0.32					
3	901	0.151	1.66	0.87	0.83	0.37					
4	874	0.153	1.64	0.87	0.82	0.31					
5	898	0.153	1.64	0.88	0.82	0.36					
6	911	0.156	1.65	0.86	0.84	0.33					
7	1039	0.152	1.62	0.88	0.83	0.35					
8	903	0.156	1.61	0.87	0.85	0.38					
9	908	0.155	1.63	0.88	0.85	0.35					
10	1011	0.152	1.63	0.86	0.82	0.32					
11											
12											
13											
14											
15											
X	931.7	0.1544	1.634	0.873	0.836	0.344					
R	165	0.007	0.05	0.02	0.04	0.07					
CUSTOMER											
SAMPLE											

#### TEST INSTRUMENT:

HP4291A RF IMPEDANCE / MATERIAL ANALYZER FOR Z  
CHEN HWA 502BC / HP4338B FOR RDC

#### APPEARANCE AND DIMENSIONS :

SPEC : MEET ITEM 6.

TEST METHOD : VISUAL INSPECTION AND MEASURED WITH SILDE CALIPERS.

#### TESTING CONDITIONS :

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature (15 to 35°C)	20 $\pm$ 2 °C
Humidity	Ordinary Humidity (25 to 85 %RH)	60 to 70 %RH




# YAGEO CORPORATION

## SBK160808T Series Specification

### 11 PACKAGING

#### 11.1 Packaging -Cover tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



#### 11.2 Packaging Quantity

TYPE	BULK	CHIP / REEL
SB100505	✓	10000
SB160808	✓	4000
SB201209	✓	4000
SB201212	✓	3000
SB321611	✓	3000
SB321616	✓	2000
SB322513	✓	2500
SB451616	✓	2000
SB453215	✓	1000

#### 11.3 Reel Dimensions



Dimensions in mm


TYPE	A	B	C	D
SB100505	178	60	10	2
SB160808	178	60	10	2
SB201209	178	60	10	2
SB201212	178	60	10	2
SB321611	178	60	10	2
SB321616	178	60	10	2
SB322513	178	60	10	2
SB451616	178	60	14	2
SB453215	178	60	14	2

# YAGEO CORPORATION

## SBK160808T Series Specification

### 11 PACKAGING

#### 11.4 Tape Dimensions in mm



TYPE	A	B	T	W	P	F	K	Tape Typ.
SB100505	0.65	1.15	0.60	8	2	3.5		B
SB160808	1.10	1.85	0.95	8	4	3.5		B
SB201209	1.50	2.30	0.97	8	4	3.5		B
SB201212	1.35	2.25	0.22	8	4	3.5	1.35	A
SB321611	1.88	3.50	0.22	8	4	3.5	1.27	A
SB321616	1.88	3.53	0.22	8	4	3.5	1.80	A
SB322513	2.77	3.42	0.22	8	4	3.5	1.55	A
SB451616	1.93	4.95	0.24	12	4	5.5	1.93	A
SB453215	3.66	4.95	0.24	12	8	5.5	1.85	A

### 12 Recommended Pattern

### 13 Note:

1. Please make sure that your product is has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)

# YAGEO CORPORATION

## SBK160808T Series Specification

### 14 Curve:

