

**MICROOPTO
MOS 24VDC/5-33VDC 10A**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com



The MICROOPTO SOLENOID solid-state relay is used especially as switching amplifier for actuators up to 24 V DC and 10 A with inductive loads such as solenoid valves and contactors. A potential-free signalling contact transmits errors, such as short circuit to the controller. The MICROOPTO SOLENOID solid-state relay is short-circuit-proof and protected against power-related transients and voltage peaks by extensive protective circuits. The closed housing also offers a high level of protection against contact.

General ordering data

Order No.	8937940000
Part designation	MOS 24VDC/5-33VDC 10A
Version	MICROOPTO, Solid-state relay, 5...33 V DC, 10 A, Screw connection
GTIN (EAN)	4032248716173
Qty.	1 pc(s).

MICROOPTO MOS 24VDC/5-33VDC 10A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions

Length	90 mm	Width	6.1 mm
Height	98 mm		

Temperature

Ambient temperature (operational)	-25 °C...+60 °C	Storage temperature	-40 °C...+80 °C
-----------------------------------	-----------------	---------------------	-----------------

Probability of failure

MTTF	399 Years
------	-----------

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; CE
----------------------	-----------------------------------

Control side

Dropout voltage	< 13 V	Input frequency	50 Hz
Power rating	400 mW	Protective circuit, control side	Varistor, reverse polarity protection
Rated control voltage	24 V DC \pm 20 %	Status display on control side	Error LED red; Status LED green
making voltage	> 18 V		

General data

Alarm contact	5...48 V DC / 0.1 A	Standards	EN 50178 GL 2003-VI-Abs. 9 IEC 62314 UL508
Humidity	40°C / 93% rel. humidity, no condensation	Flammability class UL 94	V-0
Conductor connection system	Screw connection	Solid-state type	POWER MOS-FET

Insulation coordination (EN 50 178)

Clearance and creepage distances for control/load side	> 3 mm	Overvoltage category	III
Pollution severity	2	Rated impulse withstand voltage	4 kV (1.2 / 50 μ s)
Rated voltage	300 V		

Load side

Continuous current	10 A	Leakage current	< 1 mA
Load category	LC A	Protective circuit, load side	Varistor Current sensor
Rated switching current	10 A	Rated switching voltage	5...33 V DC
Short-circuit-proof	Resistance	Switch-off delay	typical. 700 μ s
Switch-on delay	typical. 250 μ s	Voltage drop at max. load	approx. 100 mV

Classifications

ETIM 3.0	EC001504	eClass 5.1	27-27-09-90
eClass 6.0	27-27-09-90		

Datasheet

**MICROOPTO
MOS 24VDC/5-33VDC 10A**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Notes

Note, technical data	Suppressor circuitry for inductive loads, 10-cm installation clearance to inductive switching devices
----------------------	---

Datasheet

**MICROOPTO
MOS 24VDC/5-33VDC 10A**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings

Electric symbol

