




Discontinued as of August 31, 2010

# Panasonic

ideas for life

## AUTOMOTIVE MICRO-ISO RELAY


## CM RELAYS



### FEATURES

- **Micro-ISO type terminals**
- **Small size:**  
20 mm(L)×15 mm(W)×22 mm(H)  
.787 inch(L)×.591 inch(W)×.866 inch(H)
- **Wide line-up**  
PC board and Plug-in type, Resistor and diode inside type.  
24V DC type is also available.
- **Compact and high-capacity 35A load switching**  
N.O.: 35A 14V DC, N.C.: 20A 14V DC (Sealed type)  
Min.  $5 \times 10^4$   
N.O.: 35A 14V DC, N.C.: 20A 14V DC (Flux-resistant type)  
Min.  $10^5$  \*12V DC type

- **Uses international standard ISO terminal arrangement.**  
The ISO international standard terminal arrangement is used.



### TYPICAL APPLICATIONS

- Fan motor
- Heater
- Head lamp
- Air Compressor
- EPS
- ABS
- Blower fan
- Defogger, etc.

Compliance with RoHS Directive

### SPECIFICATIONS

#### Contact

Type	12 V coil voltage	24 V coil voltage
Arrangement	1 Form A, 1 Form C	
Contact material	Ag alloy (Cadmium free)	
Initial contact resistance (Initial) (By voltage drop 6 V DC 1 A)	Typ. 2 mΩ	
Contact voltage drop	Max. N.O.: 0.5 V (at 35 A 14 V DC) Max. N.C.: 0.3 V (at 20 A 14 V DC)	Max. N.O.: 0.3 V (at 15 A 28 V DC) Max. N.C.: 0.2 V (at 8 A 28 V DC)
Rating (resistive load)	Nominal switching capacity	N.O.: 35 A 14 V DC N.C.: 20 A 14 V DC
	Max. carrying current	N.O.: 20 A (14 V DC, at 85°C 185°F) N.C.: 10 A (14 V DC, at 85°C 185°F)
	Min. switching capacity <sup>#1</sup>	1 A 12 V DC
Expected life	Mechanical (at 120 cpm)	Min. $10^6$
	Electrical (at rated load)	Flux-resistant type: Min. $10^5$ *1 Sealed type: Min. $5 \times 10^4$

#### Coil

	1.5 W 1.7 W (with resistor inside type)	1.8 W 2.0 W (with resistor inside type)
Nominal operating power		

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

#### Characteristics

Type	24V coil type	12V coil type
Max. operating speed (at nominal switching capacity)	15 cpm	
Initial insulation resistance*2	Min. 20 MΩ (at 500 V DC)	
Initial breakdown voltage*3	Between open contacts	500 Vrms for 1 min.
	Between contacts and coil	500 Vrms for 1 min.
Operate time*4 (at nominal voltage) (at 20°C 85°F)	Max. 10 ms (initial)	
Release time*4 (at nominal voltage) (at 20°C 85°F)	Max. 10 ms Max. 15 ms (with diode) (initial)	
Shock resistance	Functional*5	Min. 200 m/s <sup>2</sup> {20G}
	Destructive*6	Min. 1,000m/s <sup>2</sup> {100G}
Vibration resistance	Functional	10 Hz to 500 Hz, Min. 44.1 m/s <sup>2</sup> {4.5 G}
	Destructive*7	10 Hz to 2,000 Hz, Min. 44.1 m/s <sup>2</sup> {4.5 G}
Conditions for operation, transport and storage*8 (Not freezing and condensing at low temperature)	Ambient temp.	-40°C to + 85°C -40°F to + 185°F
	Humidity	5% R.H. to 85% R.H.
Mass	Approx. 20g .71oz	

#### Remarks

- \*1 At nominal switching capacity, operating frequency: 2s ON, 2s OFF
- \*2 Measurement at same location as "Initial breakdown voltage" section.
- \*3 Detection current: 10mA
- \*4 Excluding contact bounce time.
- \*5 Half-wave pulse of sine wave: 11 ms; detection time: 10 μs
- \*6 Half-wave pulse of sine wave: 6 ms
- \*7 Time of vibration for each direction; X, Y, Z direction: 4 hours



\*8 Refer to Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT  
Please inquire if you will be using the relay in a high temperature atmosphere.



## ORDERING INFORMATION

CM 1 F — R — P — 12V				
Contact arrangement	Protective construction	Classification of types	Mounting classification	Coil voltage (DC)
1a: 1 Form A 1: 1 Form C	Nil: Sealed type F: Flux-resistant type	Nil: Standard type D: with diode inside R: with resistor inside	Nil: Plug-in type P: PC board type	12 V 24 V

Note: Bulk package: 50 pcs.; Case: 200 pcs.

## TYPES

Packing quantity: Inner 50pcs, Outer 200pcs.

Contact arrangement	Part No.	Coil voltage	Mounting classification	Protective construction
1 Form A	CM1a-12V	12 V DC	Plug-in type	Sealed type
	CM1aF-12V			Flux-resistant type
	⚠ CM1a-P-12V		PC board type	Sealed type
	⚠ CM1aF-P-12V			Flux-resistant type
1 Form C	CM1-12V		Plug-in type	Sealed type
	CM1F-12V			Flux-resistant type
	⚠ CM1-P-12V		PC board type	Sealed type
	⚠ CM1F-P-12V			Flux-resistant type

Contact arrangement	Part No.	Coil voltage	Mounting classification	Protective construction
1 Form A	CM1a-24V	24 V DC	Plug-in type	Sealed type
	CM1aF-24V			Flux-resistant type
	CM1a-P-24V		PC board type	Sealed type
	CM1aF-P-24V			Flux-resistant type
1 Form C	CM1-24V		Plug-in type	Sealed type
	CM1F-24V			Flux-resistant type
	CM1-P-24V		PC board type	Sealed type
	CM1F-P-24V			Flux-resistant type


## COIL DATA (at 20°C 68°F)

Nominal voltage, V DC	Pick-up voltage, V DC	Drop-out voltage, V DC	Nominal current, mA	Coil resistance, ohm	Nominal operating power, W	Usable voltage range, V DC
12	3 to 7	1.2 to 4.2	125±10%	96±10%	1.5	10 to 16
24	6 to 14	2.4 to 8.4	75±10%	320±10%	1.8	20 to 32

## DIMENSIONS

mm inch

## 1. Micro-ISO Plug-in type (1 Form C)



## Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch: ±0.2 ±.008

Min. 3mm .118 inch:


## General tolerance

±0.1 ±.004

±0.2 ±.008

±0.3 ±.012

## Schematic (Bottom view)



\* Intervals between terminals is measured at A surface level.




Discontinued as of August 31, 2010

CM

## 2. Micro-ISO Plug-in type (1 Form A)

mm inch



### Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch:  $\pm 0.2 \pm 0.08$

Min. 3mm .118 inch:


### General tolerance

$\pm 0.1 \pm 0.04$

$\pm 0.2 \pm 0.08$


$\pm 0.3 \pm 0.12$

### Schematic (Bottom view)



\* Intervals between terminals is measured at A surface level.

## 3. Micro-ISO PC board type (1 Form C)



### Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch:  $\pm 0.2 \pm 0.08$

Min. 3mm .118 inch:


### General tolerance

$\pm 0.1 \pm 0.04$


$\pm 0.2 \pm 0.08$

$\pm 0.3 \pm 0.12$

### Schematic (Bottom view)




### PC board pattern (Bottom view)



\* Dimensions (thickness and width) of terminal specified in this catalog is measured before pre-soldering.  
Intervals between terminals is measured at A surface level.

## 4. Micro-ISO PC board type (1 Form A)



### Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch:  $\pm 0.2 \pm 0.08$

Min. 3mm .118 inch:


### General tolerance

$\pm 0.1 \pm 0.04$

$\pm 0.2 \pm 0.08$

$\pm 0.3 \pm 0.12$

### Schematic (Bottom view)



\* Dimensions (thickness and width) of terminal specified in this catalog is measured before pre-soldering.  
Intervals between terminals is measured at A surface level.



## REFERENCE DATA


### 1-(1). Coil temperature rise (12V type)

Sample: CM1F-12V, 3 pcs.

Measured portion: Inside the coil

Contact carrying current: 20A, 35A

Ambient temperature: 85°C 185°F




### 1-(2). Coil temperature rise (24V type)

Sample: CM1F-24V, 4 pcs.


Measured portion: Inside the coil

Contact carrying current: 0A, 15A


Ambient temperature: 85°C 185°F




### 2. Max. switching capability (Resistive load, initial)



### 3. Ambient temperature and operating temperature range (12V type)




### 4. Ambient temperature characteristics (Cold/initial)



### 5. Distribution of pick-up and drop-out voltage


Sample: CM1F-12V, 100pcs.



### 6. Distribution of operate time

Sample: CM1F-12V, 30pcs.

\* Max. 10ms standard (excluding contact bounce)




### 7. Distribution of release time

Sample: CM1F-12V, 30pcs.

\* Max. 10ms standard (excluding contact bounce)

Without diode





Discontinued as of August 31, 2010

CM

#### 8-(1). Electrical life test (Motor free)

Sample: CM1aF-R-12V, 6pcs.


Load: 16 A 13.5 V DC

Cooling fan motor actual load (free condition)

Switching frequency: (ON:OFF = 2s:6s)


Ambient temperature: Room temperature

#### Circuit




#### Load current waveform


Inrush current: 85A, Steady current: 18A,



#### Change of pick-up and drop-out voltage



#### Change of contact resistance



#### 8-(2). Electrical life test (Halogen lamp load)


Sample: CM1aF-R-12V, 6pcs.

Load: 20A 13.5V DC


Switching frequency: (ON:OFF = 1s:14s)

Ambient temperature: Room temperature

#### Change of pick-up and drop-out voltage



#### Change of contact resistance



## Cautions regarding the protection element

### 1. Part numbers without protection elements

#### 1) 12 V models

When connecting a coil surge protection circuit to these relays, we recommend a Zener diode with a Zener voltage of 24 V or higher, or a resistor (680Ω to 1,000Ω). When a diode is connected to the coil in parallel, the release time will slow down and working life may shorten. Before use, please check the circuit and verify that the diode is not connected in parallel to the coil drive circuit.

#### 2) 24 V models

When connecting a coil surge protection

circuit to these relays, we recommend a Zener diode with a Zener voltage of 48 V or higher, or a resistor (2,800Ω to 4,700Ω).

When a diode is connected to the coil in parallel, the release time will slow down and working life may shorten. Before use, please check the circuit and verify that the diode is not connected in parallel to the coil drive circuit.

### 2. Part numbers with diodes

These relays use a diode in the coil surge protection element. Therefore, the release time is slower and the working life might be shorter compared to part

numbers without protection elements and part numbers with resistors.

Be sure to use only after evaluating under actual load conditions.

### 3. Part numbers with resistors

This part number employs a resistor in the coil surge protection circuit; therefore, an external surge protection element is not required. In particular, when a diode is connected in parallel with a coil, the revert time becomes slower which could adversely affect working life. Please check the circuit and make sure that a diode is not connected in parallel with the coil drive circuit.

## For Cautions for Use, see Relay Technical Information.