





Product Sheet

Part Number: CSHF 16



Dimensions in mm



| | |
|----------------------------------|--|
| Family | inserts |
| Version | Spring connection contacts SQUICH |
| Series | CSH |
| Product type | with female contacts |
| Model | female insert |
| Reference standard | EN 61984 (2001-11) |
| Contact type | silver plated |
| No. of poles | 16 poles +  |
| Voltage (V) | 500V |
| Current (A) | 16A (A.C. and D.C.) |
| Wire section | 0,14mm ² - 2,5mm ² |
| Awg size | 26 - 14 |
| Quality mark |  [®] us 600V  |
| IP degree of protection | IP20 degree of protection without enclosure; IP65, IP66, IP68 (EN 60529) and IP69K (DIN 40050 - 9) with enclosure |
| Fixing centre distance | size "77.27" |
| Impulse withstand voltage | 6kV |
| Pollution degree | 3 |

The information and the dimensions are not binding and may be changed without prior notice.