






P-Channel 1.8-V (G-S) MOSFET

PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
-8	0.035 @ $V_{GS} = -4.5$ V	± 7.1
	0.047 @ $V_{GS} = -2.5$ V	± 6.2
	0.062 @ $V_{GS} = -1.8$ V	± 5.7

TrenchFET[®]
Power MOSFETs
1.8-V Rated



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)					
Parameter		Symbol	5 secs	Steady State	Unit
Drain-Source Voltage		V_{DS}	-8		V
Gate-Source Voltage		V_{GS}	± 8		
Continuous Drain Current ($T_J = 150^\circ\text{C}$) ^a	$T_A = 25^\circ\text{C}$	I_D	± 7.1	± 5.2	A
	$T_A = 85^\circ\text{C}$		± 5.2	± 3.7	
Pulsed Drain Current		I_{DM}	± 20		
Continuous Source Current ^a		I_S	-2.1	-1.1	W
Maximum Power Dissipation ^a	$T_A = 25^\circ\text{C}$	P_D	2.5	1.3	
	$T_A = 85^\circ\text{C}$		1.3	0.7	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 150		$^\circ\text{C}$

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^a	$t \leq 5$ sec	R_{thJA}	40	50	$^\circ\text{C/W}$
	Steady State		80	95	
Maximum Junction-to-Foot (Drain)	Steady State	R_{thJF}	15	20	

Notes

a. Surface Mounted on 1" x 1" FR4 Board.





SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250 μA	-0.45			V
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ±8 V			±100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = -6.4 V, V _{GS} = 0 V			-1	μA
		V _{DS} = -6.4 V, V _{GS} = 0 V, T _J = 85 °C			-5	
On-State Drain Current ^a	I _{D(on)}	V _{DS} ≤ -5 V, V _{GS} = -4.5 V	-20			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = -4.5 V, I _D = -5.2 A		0.030	0.035	Ω
		V _{GS} = -2.5 V, I _D = -4.5 A		0.040	0.047	
		V _{GS} = -1.8 V, I _D = -2 A		0.052	0.062	
Forward Transconductance ^a	g _{fs}	V _{DS} = -5 V, I _D = -5.2 A		18		S
Diode Forward Voltage ^a	V _{SD}	I _S = -1.1 A, V _{GS} = 0 V		-0.8	-1.2	V
Dynamic^b						
Total Gate Charge	Q _g	V _{DS} = -4 V, V _{GS} = -4.5 V, I _D = -5.2 A		17	26	nC
Gate-Source Charge	Q _{gs}			2.8		
Gate-Drain Charge	Q _{gd}			2.6		
Turn-On Delay Time	t _{d(on)}	V _{DD} = -4 V, R _L = 4 Ω I _D ≅ -1 A, V _{GEN} = -4.5 V, R _G = 6 Ω		15	25	ns
Rise Time	t _r			45	70	
Turn-Off Delay Time	t _{d(off)}			110	165	
Fall Time	t _f			65	100	
Source-Drain Reverse Recovery Time	t _{rr}		I _F = -1.1 A, di/dt = 100 A/μs		30	

Notes

- a. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.
- b. Guaranteed by design, not subject to production testing.


TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)






TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)


On-Resistance vs. Drain Current




Capacitance




Gate Charge




On-Resistance vs. Junction Temperature



Source-Drain Diode Forward Voltage



On-Resistance vs. Gate-to-Source Voltage





TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

