



## Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 5

99C C502 5C 0.7MM 0.5KG RLR

sds no. : 185372

V003.0

Revision: 20.05.2010

printing date: 23.10.2010

### 1. Identification of the substance/preparation and of the company/undertaking

**Trade name:**

99C C502 5C 0.7MM 0.5KG RLR

**Intended use:**

Solder Wire

**Company name:**

Henkel Limited  
Technologies House  
Wood Lane End  
HP2 4 RQ Hemel Hempstead

Great Britain

Phone: +44 (14422780) 00

Fax-no.: +44 (14422780) 71

**E-mail address of person responsible for Safety Data Sheet:**

ua-productsafety.uk@uk.henkel.com

**Emergency information:**

24 Hours Emergency Tel: +44 (0)1442 278497

### 2. Hazards identification

The product is not hazardous within the meaning of the valid (EU) preparation directive.

This product contains modified rosin.

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs. Prolonged or repeated exposure to flux fumes may result in sensitisation in sensitive workers.

### 3. Composition / information on ingredients

**Declaration of ingredients according to (EC) No 1907/2006:**

Hazardous components CAS-No.	EINECS ELINCS	content	Classification
Tin 7440-31-5	231-141-8	90 - 100 %	
Copper 7440-50-8	231-159-6	0,1 - 1 %	R52/53 Xn - Harmful; R22 Xi - Irritant; R36/37/38

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

### 4. First aid measures

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.  
Obtain medical attention if irritation persists.

**Eye contact:**

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

**Ingestion:**

Do not induce vomiting.  
Seek medical advice.

## 5. Fire fighting measures

**Combustion behaviour:**

The product itself does not burn. Any fire extinguishing action should be appropriate to the surroundings.

**Extinguishing media which must not be used for safety reasons:**

Do not use water on fires where molten metal is present.

**Special protection equipment for firefighters:**

Wear self-contained breathing apparatus.

**Hazardous combustion products:**

High temperatures may produce heavy metal dust, fumes or vapours.  
The flux medium will give rise to irritating fumes.

## 6. Accidental release measures

**Personal precautions:**

Avoid contact with skin and eyes.

**Environmental precautions:**

Do not empty into drains / surface water / ground water.

**Clean-up methods:**

Scrape up spilled material and place in a closed container for disposal.

## 7. Handling and storage

**Handling:**

Extraction is necessary to remove fumes evolved during reflow.  
When using do not eat, drink or smoke.  
Wash hands before breaks and immediately after handling the product.

**Storage:**

Store in a cool, dry place.

**8. Exposure controls / personal protection****Components with specific control parameters for workplace:**

Valid for  
Great Britain  
Basis  
UK EH40 WELs

Ingredient	ppm	mg/m3	Type	Category	Remarks
TIN (INORGANIC COMPOUNDS AS SN) 7440-31-5		2	Time Weighted Average (TWA).	Indicative	ECTLV
COPPER, INHALABLE DUSTS AND MISTS (AS CU) 7440-50-8		2	Short Term Exposure Limit (STEL):		EH40 WEL
COPPER, FUME 7440-50-8		0,2	Time Weighted Average (TWA).		EH40 WEL
COPPER, INHALABLE DUSTS AND MISTS (AS CU) 7440-50-8		1	Time Weighted Average (TWA).		EH40 WEL

**Engineering controls:**

Extraction is necessary to remove fumes evolved during reflow.  
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.

**Respiratory protection:**

In case of insufficient ventilation, wear suitable respiratory equipment.

**Hand protection:**

The use of chemical resistant gloves such as Nitrile are recommended.  
Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

**9. Physical and chemical properties****General characteristics:**

Appearance solid

Odor: Grey  
None

**Phys./chem. properties:**

pH-value not applicable  
Flash point none  
Vapor pressure not applicable  
Density 7,3 g/cm3  
(25 °C (77 °F))  
Solubility (qualitative) Insoluble  
(Solvent: Water)  
Melting point 227 °C (440.6 °F)  
Octanol/Water distribution coefficient Not applicable  
Vapor density: Heavier than air  
VOC content < 5,0 %

**10. Stability and reactivity****Conditions to avoid:**

Stable under recommended storage conditions.

**Materials to avoid:**

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

**Hazardous decomposition products:**

Thermal decomposition can lead to release of irritating gases and vapors.

### 11. Toxicological information

**Oral toxicity:**

This material is considered to have low toxicity if swallowed.

**Inhalative toxicity:**

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs. Prolonged or repeated exposure to flux fumes may result in sensitisation in sensitive workers.

**Dermal toxicity:**

This product is considered to have low dermal toxicity.

**Skin irritation:**

Fumes emitted during soldering may irritate the skin.

**Eye irritation:**

Fumes emitted during soldering may irritate the eyes.

### 12. Ecological information

**Mobility:**

The product is insoluble and sinks in water.

**Persistence and Biodegradability:**

The product is not biodegradable.

**Bioaccumulative potential:**

Octanol/Water distribution coefficient: Not applicable

**Ecotoxicity:**

Hazardous components CAS-No.	Species	Exposure time	Value type	Value
Copper 7440-50-8	Bluegill (Lepomis macrochirus)	96 h	LC 50	10 mg/l

### 13. Disposal considerations

**Product disposal:**

Wherever possible unwanted solder alloy should be recycled for recovery of metal.  
Otherwise dispose of in accordance with local and national regulations.

**Waste code(EWC ):**

06 04 05 - wastes containing other heavy metals

**Disposal of uncleaned packages:**

Dispose of as unused product.

### 14. Transport information

**General information:**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.



## 15. Regulations - classification and identification

### Indication of danger:

none

### Risk phrases:

not applicable

### Safety phrases:

not applicable

### Additional information:

Avoid breathing fumes given out during soldering.

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

After handling solder wash hands with soap and water before eating, drinking or smoking.

Keep out of reach of children.

### National regulations/information (Great Britain):

#### Remarks

The Health & Safety at Work Act 1974.

The Control of Substances Hazardous to Health Regulations. L5:General  
Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step  
Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to  
control chemicals.

IND (G)248L: Solder fume and you. IND(G)249L: Controlling health risks from  
rosin (colophony) based solder fluxes.

## 16. Other information

The labelling of the product is indicated in Section 15. The full text of the R-phrases indicated by codes in this safety data sheet are as follows:

R22 Harmful if swallowed.

R36/37/38 Irritating to eyes, respiratory system and skin.

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.