



### Specifications:

Bandwidth	150MHz
Rise Time	≤2.3ns
Sample Range	500MS/s
Vertical Sensitivity	2mV ~ 5V/div
Maximum Record Length	1024k
Sample Rate	Real time 500MS/s, Equivalent : 25GS/s
Scan Time Base	2ns ~ 50s/div
Trigger Type	Edge, Pulse, Video and Alternate
Automatic Waveform Measurements	28
Ports	Standard : USB Device USB Host : RS-232C Optional : LAN
Mathematics	Add, Subtract, Multiply, Divide, Reverse and FFT
Applications	College Education, R&D, Electronic Product Assemble Line, Industrial Control etc
Display	64k, Full Colour LCD 320 x 240

### General Characteristics:

Power	100 - 240V <sub>rms</sub> ac, 45Hz - 440Hz, CAT II
LCD Size	Diagonal 145mm (5.7 inches)
Colour	Red and Grey, White and Grey
Size	320mm (wide) x 150mm (high) x 130mm (deep)
Standard Accessories	Probe x 2 (1x, 10x Switchable; Optional Purchase; 100x probe), Power Cord and English Manual

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of the Group. © Premier Farnell plc 2009.