
### **DISCRETE SEMICONDUCTORS**

# DATA SHEET



## BSR40; BSR41; BSR42; BSR43 NPN medium power transistors

Product data sheet Supersedes data of 1999 Apr 28 2004 Dec 13



### NPN medium power transistors

BSR40; BSR41; BSR42; BSR43

### **FEATURES**

- High current (max. 1 A)
- Low voltage (max. 80 V).

### **APPLICATIONS**

- Thick and thin-film circuits
- Telephony and general industrial applications.

### **DESCRIPTION**


NPN medium power transistor in a SOT89 plastic package. PNP complements: BSR30; BSR31 and BSR33.

### **MARKING**

TYPE NUMBER	MARKING CODE	TYPE NUMBER	MARKING CODE		
BSR40	AR1	BSR42	AR3		
BSR41	AR2	BSR43	AR4		

### **PINNING**

PIN	DESCRIPTION
1	emitter
2	collector
3	base



### **ORDERING INFORMATION**

TYPE NUMBER	PACKAGE					
NAME		DESCRIPTION	VERSION			
BSR40	SC-62	plastic surface mounted package; collector pad for good heat	SOT89			
BSR41		transfer; 3 leads				
BSR42						
BSR43						

### NPN medium power transistors

BSR40; BSR41; BSR42; BSR43

#### LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V <sub>CBO</sub>	collector-base voltage	open emitter			
	BSR40; BSR41		_	70	V
	BSR42; BSR43		_	90	V
V <sub>CEO</sub>	collector-emitter voltage	open base			
	BSR40; BSR41		_	60	V
	BSR42; BSR43		_	80	V
V <sub>EBO</sub>	emitter-base voltage	open collector	_	5	V
I <sub>C</sub>	collector current (DC)		_	1	А
I <sub>CM</sub>	peak collector current		_	2	А
I <sub>BM</sub>	peak base current		_	0.2	Α
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> ≤ 25 °C; note 1	-	1.35	W
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature			150	°C
T <sub>amb</sub>	ambient temperature		-65	+150	°C

### Note

### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R <sub>th(j-a)</sub>	thermal resistance from junction to ambient	note 1	93	K/W
R <sub>th(j-s)</sub>	thermal resistance from junction to soldering point		13	K/W

### Note

Device mounted on a printed-circuit board, single-sided copper, tin-plated, mounting pad for collector 6 cm<sup>2</sup>.
 For other mounting conditions, see "Thermal considerations for SOT89 in the General Part of associated Handbook".

<sup>1.</sup> Device mounted on a printed-circuit board, single-sided copper, tin-plated, mounting pad for collector 6 cm<sup>2</sup>. For other mounting conditions, see "Thermal considerations for SOT89 in the General Part of associated Handbook".

### NPN medium power transistors

BSR40; BSR41; BSR42; BSR43

### **CHARACTERISTICS**

 $T_{amb}$  = 25 °C unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
I <sub>CBO</sub>	collector-base cut-off current	I <sub>E</sub> = 0 A; V <sub>CB</sub> = 60 V	_	100	nA
		I <sub>E</sub> = 0 A; V <sub>CB</sub> = 60 V; T <sub>j</sub> = 150 °C	_	50	μΑ
I <sub>EBO</sub>	emitter-base cut-off current	I <sub>C</sub> = 0 A; V <sub>EB</sub> = 5 V	_	100	nA
h <sub>FE</sub>	DC current gain	$I_C = 100 \mu A$ ; $V_{CE} = 5 V$ ; note 1			
	BSR40; BSR42		10	_	
	BSR41; BSR43		30	_	
	DC current gain	I <sub>C</sub> = 100 mA; V <sub>CE</sub> = 5 V; note 1			
	BSR40; BSR42		40	120	
	BSR41; BSR43		100	300	
	DC current gain	$I_C = 500 \text{ mA}; V_{CE} = 5 \text{ V}; \text{ note 1}$			
	BSR40; BSR42		30	_	
	BSR41; BSR43		50	_	
V <sub>CEsat</sub>	collector-emitter saturation voltage	I <sub>C</sub> = 150 mA; I <sub>B</sub> = 15 mA; note 1	_	250	mV
		$I_C = 500 \text{ mA}$ ; $I_B = 50 \text{ mA}$ ; note 1	_	500	mV
V <sub>BEsat</sub>	base-emitter saturation voltage	I <sub>C</sub> = 150 mA; I <sub>B</sub> = 15 mA; note 1	_	1	V
		I <sub>C</sub> = 500 mA; I <sub>B</sub> = 50 mA; note 1	_	1.2	V
C <sub>c</sub>	collector capacitance	I <sub>E</sub> = i <sub>e</sub> = 0 A; V <sub>CB</sub> = 10 V; f = 1 MHz	_	12	pF
C <sub>e</sub>	emitter capacitance	$I_C = I_c = 0 \text{ A}; V_{EB} = 0.5 \text{ V}; f = 1 \text{ MHz}$	_	90	pF
f <sub>T</sub>	transition frequency	I <sub>C</sub> = 50 mA; V <sub>CE</sub> = 10 V; f = 100 MHz	100	_	MHz
Switching	times (between 10% and 90% levels	s)			
t <sub>on</sub>	turn-on time	I <sub>Con</sub> = 100 mA; I <sub>Bon</sub> = 5 mA;	_	250	ns
t <sub>off</sub>	turn-off time	I <sub>Boff</sub> = -5 mA	_	1	μS

### Note

1. Pulse test:  $t_p \leq 300~\mu s;~\delta \leq 0.01.$ 


### NPN medium power transistors

BSR40; BSR41; BSR42; BSR43

### **PACKAGE OUTLINE**

### Plastic surface-mounted package; collector pad for good heat transfer; 3 leads

SOT89



UNIT	Α	b <sub>p1</sub>	b <sub>p2</sub>	b <sub>p3</sub>	С	D	E	е	e <sub>1</sub>	HE	Lp	w
mm	1.6 1.4	0.48 0.35	0.53 0.40	1.8 1.4	0.44 0.23	4.6 4.4	2.6 2.4	3.0	1.5	4.25 3.75	1.2 0.8	0.13

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT89		TO-243	SC-62			<del>04-08-03</del> 06-03-16

2004 Dec 13 5

### NPN medium power transistors

BSR40; BSR41; BSR42; BSR43

#### **DATA SHEET STATUS**

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### **Notes**

- 1. Please consult the most recently issued document before initiating or completing a design.
- 2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### **DISCLAIMERS**

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

### **NXP Semiconductors**

### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

### **Contact information**

For additional information please visit: http://www.nxp.com
For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands R75/04/pp7 Date of release: 2004 Dec 13 Document order number: 9397 750 13874

