




Top View of Assembly




SECTION A-A End View of Assembly




1554N




SECTION B-B Side View of Assembly




Top View Looking Inside Box



Lid




Available 16 Gauge Steel Plate



NOTE: Hole patterns same as seen in top view of box.

Maximum P.C. Board Size



NOTE	
Purchased assembly includes box, lid and 4 cover screws.	
Cover screws should be torqued to 2.5 lbf-in (30 cN-m)	
Polycarbonate version is 508 approved	
Enclosure Type 4X, 4, 12 File# E65324	

1554N	
1554N Regular Enclosure	
General Purpose ABS	1554NGY
Polycarbonate	1554N2GY
1554N Clear Lid Enclosure	
Polycarbonate	1554N2GYCL
ACCESSORIES	
Heavy Duty 16 Gauge Galvanized Steel Panels	1554NPL
Steel Panel / P.C. Board Machine Screw [M3 X 8mm Nickel Plated]	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Nickel Plated]	1598ATS100
Cover Screws (Pkg 4) [M4 X 20mm Stainless Steel]	SC1554

