

# Electronics Super-Knips

DIN ISO 9654

78 81 125



78 91 125



- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- precision shaped tips also cut close sitting wire from 0.2 mm dia.
- joint with stainless steel rivet
- extremely smooth movement for minimum operator fatigue
- with opening spring and restricted opening







## Model: 78 71 125

- special tool steel, burnished
- with lead catcher - no uncontrolled loss of cut wire ends
- precision-ground cutting edges without bevel for flush cutting
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC

## Model: 78 81 125

- precision ground cutting edges with very small bevel suitable also for hard wire
- special tool steel, burnished
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC



Article- No.	EAN 4003773-	Head	Handles	Style Symbols	 Ø mm	 Ø mm	 Ø mm	B mm	A mm	D mm		Length mm	g
78 81 125	065074	polished	with two- colour dual component handles	8 	1,6	1,2	0,6	9,00	13,50	7,50	-	125	50
78 91 125	065081	polished	with two- colour dual component handles	9 	1,6	1,2	0,6	9,00	13,50	7,50	-	125	50

technical change and errors excepted