

KNIPEX 99 14 300 High Leverage Concretors' Nipper



Description:

- To Twist and cur thicker wire in one operation: fast, reliable and economical
- Very slim shape for tying submerged positioned steel rods.
- Particularly high cutting capacity with minimum effort due to optimum transmission ratio
- High damping of the cutting stroke after cutting stroke after cutting the binding wire, which reduces strain on tendons and muscles
- Cutting edges with additional hardness: cutting edge hardness approx 61 HRC
- High-grade special tool steel, forged, oil-hardened

Technical Details:

Head Width : 25mm

Length: 300mm

Diameter: 3.8mm

Weight: 499g