

AC Centrifugal Blowers Dual Inlet, Ø133mm



ebm-papst Mulfingen



- Dual Inlet fans with an external rotor motor offering the advantage of matched motor and impeller in a compact space saving design.
- Motors: IP44 rated, sealed for life, maintenance free, class B insulation, precision ball bearings and side mounted capacitor and terminal block.
- Impeller: forward curved multi-vane type force fitted for vibration free operation/efficient cooling.
- Body: heavy duty, galvanised steel
- May be mounted in any position

Nominal Data		Curve	Voltage	Frequency	Air Flow	Speed/rpm	Power Input	Current Draw	Noise	Perm. Amb. Temp.	Mass
Part Number	Curve	VAC	HZ	M ³ /h	min ⁻¹	W	A	DB(A)	°C	kg	
D2E133-CI33-87	2	230	50	700	1700	175	0.77	58	40	3.3	
		230	60	500	2100	190	0.84	58	40		
D2E133-DM27-D8	3	230	50	810	1150	190	0.84	56	40	4.4	
		230	60	600	1550	195	0.85	55	40		

AC Centrifugal Blowers

Dual Inlet, Ø133mm

Performance Curve



Dimensions

Part Number	A	B	C	D	E	I	J	K	L	M	N	P
D2E133-CI33-87	206	190	142	126	102	168	400	204	97	213	93.5	67.5
D2E133-DM27-D8	270	254	142	126	102	232	300	204	97	213	98	67.5

