


P.C.B. HOLE DIM. FOR CONTACTS

DRILLED HOLE :	1,15 ± 0,025 mm
FIN. HOLE :	0,94 to 1,09 mm
AFTER REFLOW :	0,91 to 1,09 mm
Cu-thks :	0,025 to 0,075 mm
SnPb-thks :	0,004 to 0,010 mm



DO NOT SCALE METRIC THIRD ANGLE PROJECTION

DIMENSIONS IN mm

ACCESSORIES PREFIX	ITEM NR.	DESCRIPTION OF ACCESSORY	QTY	UNIT
	4	BUSHING-- PRESSLOCK 4-40 UNC THREAD	2	
	4	BUSHING-- PRESSLOCK M3 THREAD	2	
	5	FEM. SCRL.-- PRESSLOCK 4-40 UNC THREAD	2	
	5	FEM. SCRL.-- PRESSLOCK M3 THREAD	2	

HOW TO ORDER:

9 POS.-----> Z-188987-Y

PREFIX FOR ACCESSORIES

BASIC PARTNR.

SUFFIX FOR PLATING

PLATING SUFFIX "Y"

GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652) } -Y = -2
PRESS-FIT PART: 2,5µm BRIGHT SnPb.

NOTES :

① CAVITY IDENTIFICATION AT FRONT SIDE ONLY.

② PARTNUMBER AND DATE CODE.

③ GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD, WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.

4 CONN. CAN BE USED FOR PCB THICKNESS OF 1,6 THRU 2,4 mm

ITEM NRS./MATERIAL :

① SHELL	= BRIGHT TINPLATED STEEL.
② HOUSING	= GLASSFILLED POLYESTER, COLOR : BLACK.
③ CONTACTS	= PHOSPHORBRONZE, (PLATING : SEE TABLE ABOVE).
④ BUSHING PRESS-LOCK TYPE	= TINPLATED BRASS, (INNER THREAD M3 OR 4-40 UNC).
⑤ FEMALE SCREWLOCK PRESS-LOCK TYPE	= TINPLATED BRASS, (INNER THREAD M3 OR 4-40 UNC).
⑥ STAND OFF	= ULTRAMID V0 COLOR : BLACK.

CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED			
© COPYRIGHT 19 - BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION			
AMP		AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.	
E	EH00-1417-99	P.W.	W.C. 19-02-00
D	EH-0033-99	D.K.	W.S. 28 JAN 99
LTR.	REVISION RECORD	DR.	CHK. DATE
DR.:	D.KESSLER	CHK.:	W.S.
DATE:	28 JAN 99	DATE:	18/04/00
APP.:		DATE:	
DWG.No.	C-188987	REV.LTR.	SHEET
		E	1 of 1

11 10 9 8 7 6 5 4 3 2 1