



CIRCUIT SIZE	DIM. 'A'	DIM. 'B'	DIM. 'C'
2	—	.21 (5.4)	
4	.17 (4.2)	.38 (9.6)	
6	.33 (8.4)	.54 (13.8)	
8	.50 (12.6)	.71 (18.0)	
10	.66 (16.8)	.87 (22.2)	1.04 (26.4)
12	.83 (21.0)	1.04 (26.4)	1.27 (32.3)
14	.99 (25.2)	1.20 (30.6)	1.52 (38.6)
16	1.16 (29.4)	1.37 (34.8)	1.68 (42.7)
18	1.32 (33.6)	1.54 (39.0)	1.88 (47.8)
20	1.49 (37.8)	1.70 (43.2)	2.08 (52.9)
22	1.65 (42.0)	1.87 (47.4)	2.28 (58.0)
24	1.82 (46.2)	2.03 (51.6)	2.48 (63.0)

NOTES:

- HOUSING MATERIAL:
 "BLANK" - NYLON 6/6, U.L. 94V-2, COLOR: NATURAL.
 210 - NYLON 6/6, U.L. 94V-0, COLOR: NATURAL.
- TERMINAL MATERIAL: BRASS ALLOY 260
- MOUNTING OPTIONS:
 "BLANK" - NO MOUNTING
 2 - PEG MOUNT
- TERMINAL PLATING:
 "BLANK" - .000035/(.00090) MIN. TIN OVER
 .000020/(.00050) MIN. COPPER.
 * - .000100/(.00254) MIN. SELECT MATTE TIN
 *GS2 - .000015/(.00038) MIN. SELECT GOLD AND
 .000100/(.00254) MIN. SELECT MATTE TIN
 OVER .000050/(.00127) MIN. NICKEL.

LEGEND:

- 5566 - N * * * * *
- BASE NUMBER
 - CIRCUIT SIZE
 - ASSEMBLY TYPE
 A - W/O DRAIN HOLES
 B - WITH DRAIN HOLES
 - MOUNTING OPTION (SEE NOTE 5.)
 - PLATING (SEE NOTE 6.)
 - HOUSING MAT'L. (SEE NOTE 1.)
 - K - I
 - K =
 I = T

REVISED NOTES 8 EC NO: UCP2006-2601 DRAWN: ADRIAN L. 2006/05/11 CHKD: G. POLGAR 2006/05/13 APPR: J. COMERCIAL 2006/05/15	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .015	DRAWN BY RJF	DATE 8/19/87	CHECKED BY GT	DATE 8/19/87	MINI-FIT JR. VERTICAL HEADER ASSEMBLIES WITH MOUNTING PEGS MOLEX INCORPORATED		
		2 PLACES ± 0.38 ± ---	1 PLACE ± --- ± ---	APPROVED BY RAS	DATE 8/19/87	MATERIAL NO. DOCUMENT NO. SDA-5566-N*2*-*				
		ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					SHEET NO. 1 OF 4	

