



Rev	AWO #	Description	Date	Appr
-	9427	RELEASED	3/06/09	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: PA66, rated UL 94V-0
 Insulator color: Green
 Contact: Bronze, Tin plated
 Screw: Steel, M2/Zn plated

Electrical: Operation voltage: 300 VAC max
 Current rating: 12 Amps max per Pole
 Rated surge voltage: 1.6/2/3 KV

Mechanical: Torque (Lb-in): 1.73
 Solid wire: 30-16 AWG

Environmental: Operating temperature: -40°C to +105°C
 Lead free, RoHS compliant.
 Recommended soldering temp: 235°C for 5 sec.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLDS
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN DY	3/06/09
CHECKED	
APPROVED	

ADAM TECH
 909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE	TERMINAL BLOCK, PCB, VERTICAL, 3.81MM PITCH		
SIZE	PART NO.	REV.	
X	EB25-XX-B-L		
REF:	S0002AT	SCALE:	NTS
		SHEET	1 OF 1

6 5 4 3 2 1