

JTF Series



- High Power Density
- Wide 4:1 Input Range
- Operating Temperature -40 °C to +100 °C
- Single & Dual Outputs
- Standard Remote On/Off
- 1600 VDC Isolation
- High Efficiency - up to 90%

Specification

Input

Input Voltage Range	• 24 V (9-36 VDC) 48 V (18-75 VDC)
Input Current	• See table
Input Filter	• Pi network
Input Reflected Ripple	• 20 mA pk-pk through 12 μ H inductor, 5 Hz to 20 MHz

Output

Output Voltage	• See table
Output Voltage Balance	• $\pm 1\%$ max, dual output models
Minimum Load	• No minimum load required
Initial Set Accuracy	• $\pm 1.2\%$ max
Start Up Delay	• <20 ms
Start Up Rise Time	• <10 ms
Line Regulation	• $\pm 0.2\%$ max
Load Regulation	• $\pm 0.5\%$ max single, $\pm 1.0\%$ max dual
Cross Regulation	• $\pm 5\%$ on dual output models, see note 2
Transient Response	• <3% max deviation, recovery to within 1% in 250 μ s for a 25% load change
Ripple & Noise	• 85 mV pk-pk, 20 MHz BW, with 1 μ F ceramic capacitor, see note 3
Overload Protection	• >170%
Overvoltage Protection	• 3.3 V models: 3.9 V typical 5 V models: 6.2 V typical 12 V models: 15 V typical 15 V models: 18 V typical ± 12 V models: ± 15 V typical ± 15 V models: ± 18 V typical
Short Circuit Protection	• Trip & restart (hiccup) with auto recovery
Maximum Capacitive Load	• See tables
Temperature Coefficient	• $\pm 0.02/^{\circ}$ C max
Remote On/Off	• On = 3-12 V or open circuit Off <1.2 VDC or short circuit pins 1, 2 & 3

General

Efficiency	• See tables
Isolation	• 1600 VDC Input to Output 1600 VDC Input to Case 1600 VDC Output to Case
Isolation Capacitance	• 1500 pF max
Switching Frequency	• 270 kHz typical
MTBF	• >1 Mhrs to MIL-STD-217F

Environmental

Operating Temperature	• -40 °C to +105 °C, derate from 100% load at +60 °C to no load at +105 °C
Case Temperature	• +105 °C max
Storage Temperature	• -40 °C to +125 °C
Humidity	• Up to 90%, non-condensing
Cooling	• Natural convection

EMC

Emissions	• EN55022 Class A conducted with external components - see application note
ESD Immunity	• EN61000-4-2, 4 kV contact discharge Perf Criteria B
Radiated Immunity	• EN61000-4-3, Level 3 Perf Criteria A
EFT/Burst	• EN61000-4-4, Level 3 Perf Criteria B*
Surge	• EN61000-4-5, 3 V/m Perf Criteria B*
Conducted Immunity	• EN61000-4-6, 3 Vrms Perf Criteria A
Magnetic Field	• EN61000-4-8, 1 A/m Perf Criteria A

*See note 4.

Input Voltage	Output Voltage	Output Current	Input Current ⁽¹⁾		Maximum Capacitive Load	Efficiency	Model Number
			No Load	Full Load			
9-36 V	3.3 V	3.5 A	15 mA	573 mA	2000 µF	87%	JTF1224S3V3
	5.1 V	2.4 A	15 mA	581 mA	2000 µF	89%	JTF1224S05
	12.0 V	1.0 A	15 mA	574 mA	430 µF	90%	JTF1224S12
	15.0 V	0.8 A	15 mA	574 mA	300 µF	90%	JTF1224S15
	±5.0 V	±1.2 A	15 mA	595 mA	±1250 µF	87%	JTF1224D05
	±12.0 V	±0.5 A	15 mA	574 mA	±200 µF	90%	JTF1224D12
18-75 V	±15.0 V	±0.4 A	15 mA	574 mA	±120 µF	90%	JTF1224D15
	3.3 V	3.5 A	15 mA	286 mA	2000 µF	87%	JTF1248S3V3
	5.1 V	2.4 A	15 mA	290 mA	2000 µF	89%	JTF1248S05
	12.0 V	1.0 A	15 mA	287 mA	430 µF	90%	JTF1248S12
	15.0 V	0.8 A	15 mA	287 mA	300 µF	90%	JTF1248S15
	±5.0 V	±1.2 A	15 mA	297 mA	±1250 µF	87%	JTF1248D05
	±12.0 V	±0.5 A	12 mA	287 mA	±200 µF	90%	JTF1248D12
	±15.0 V	±0.4 A	15 mA	287 mA	±120 µF	90%	JTF1248D15



Notes

1. Input current measured at nominal 24 V and 48 V input.
2. When one output is set to 100% load, and the other varies between 25% and 100% load.
3. Measured with 1 µF ceramic capacitor across output rails.
4. External input capacitor required, Nippon Chemi-Con KY series, 330 µF/ 100 V or equivalent.

Mechanical Details

All dimensions are in inches (mm) Weight: 0.04 lbs (20 g) approx.

24 Pin DIL Package - Nickel Coated Copper




- Notes:
1. Pin diameter: 0.02 ±0.002 (0.5 ±0.05)
 2. Pin pitch tolerance: ±0.014 (±0.35)
 3. Case Tolerance: ±0.02 (±0.5)


Pin Connections		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin	-Vin
3	-Vin	-Vin
9	No Pin	Common
11	Not Connected	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin	+Vin
23	+Vin	+Vin

Application Notes

Derating Curve



Input Filter



Model	C1	L	C2
24 V	2.2 µF, 100 V	12 µH	2.2 µF, 100 V
48 V	2.2 µF, 100 V	12 µH	2.2 µF, 100 V

Remote On/Off

Standard ROF logic is positive
 Output On >3.0 VDC or open circuit
 Output Off <1.2 VDC or short circuit pins 1, 2 & 3