


HSK-M/-PVDF-Ex

Mettr.



ATEX



II 2G 1D



Material
Clamping insert
Seal
O-Ring
Protection

Nickel plated brass
PA (Nylon) / PVDF
Buna-N / FPM
Buna-N / FPM
IP 68 – 10 bar / IP 69K
(NEMA 6 – 150 PSIG)
within the specified clamping range



For approvals see page 162

AG	mm	Ex- Generation	GL mm	H mm	mm	HSK-M-Ex	HSK-M-Ex	HSK-M-PVDF-Ex
						-20°C – 95°C (-4°F – 203°F)	-60°C – 105°C (-76°F – 221°F)	-20°C – 130°C (-4°F – 266°F)
M 12 x 1,5	3 - 6,5	ATEX	6,5	19	14	1.610.1200.50	1.640.1200.50	1.660.1200.50
M 12 x 1,5	2 - 5	ATEX	6,5	19	14	1.610.1200.51	1.640.1200.51	1.660.1200.51
M 16 x 1,5	4 - 8	ATEX	6	21	17 / 19	1.610.1600.50	1.640.1600.50	1.660.1600.50
M 16 x 1,5	2 - 6	ATEX	6	21	17 / 19	1.610.1600.51	1.640.1600.51	1.660.1600.51
M 16 x 1,5	6 - 10	ATEX	6	22	20	1.610.1611.50	1.640.1611.50	1.660.1611.50
M 16 x 1,5	3 - 7	ATEX	6	22	20	1.610.1611.51	1.640.1611.51	1.660.1611.51
M 20 x 1,5	6 - 12	ATEX	6	23	22	1.610.2000.50	1.640.2000.50	1.660.2000.50
M 20 x 1,5	5 - 9	ATEX	6	23	22	1.610.2000.51	1.640.2000.51	1.660.2000.51
M 20 x 1,5	10 - 14	ATEX	6	24	24	1.610.2016.50	1.640.2016.50	1.660.2016.50
M 20 x 1,5	7 - 12	ATEX	6	24	24	1.610.2016.51	1.640.2016.51	1.660.2016.51
M 25 x 1,5	14 - 18	ATEX	7	26	30	1.610.2500.50	1.640.2500.50	1.660.2500.50
M 25 x 1,5	10 - 16	ATEX	7	26	30	1.610.2500.51	1.640.2500.51	1.660.2500.51
M 32 x 1,5	20 - 25	ATEX	8	31	40	1.610.3200.50	1.640.3200.50	1.660.3200.50
M 32 x 1,5	13 - 20	ATEX	8	31	40	1.610.3200.51	1.640.3200.51	1.660.3200.51
M 40 x 1,5	22 - 32	ATEX	8	37	50	1.610.4000.50	1.640.4000.50	1.660.4000.50
M 40 x 1,5	20 - 26	ATEX	8	37	50	1.610.4000.51	1.640.4000.51	1.660.4000.51
M 50 x 1,5	32 - 38	ATEX	9	37	57	1.610.5000.50	1.640.5000.50	
M 50 x 1,5	25 - 31	ATEX	9	37	57	1.610.5000.51	1.640.5000.51	
M 63 x 1,5	37 - 44	ATEX	10	38	64 / 68	1.610.6300.50	1.640.6300.50	
M 63 x 1,5	29 - 35	ATEX	10	38	64 / 68	1.610.6300.51	1.640.6300.51	

