



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO.	SPC-F005	Effective	12/21/98	Doc No.	980	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
430	A	RELEASED	HYP	11/15/00	JC	11/21/00	DJC	11/21/00

FEATURES:

1. Adjustable 0 ~ 24mA current source
2. Current calibrator drives loads up to 500 ohms
3. Large LCD display
4. Sampling time: Approx. 0.4 seconds
5. Over input indicator: "1"
6. Operating Temperature: 0°C ~ 50°C (32°F ~ 122°F)
7. Size: 185 x 78 x 38mm (7.3 x 3.0 x 1.5 Inches)
8. Weight: 265g (.58lb) including battery
9. Requires one 9V battery - not included
10. Includes cable with red & black alligator clips & instructions



Electrical Specifications (23°C ± 5°C)

Current Source

Range	Resolution	Accuracy
0 ~ 19.99 mA	0.01 mA	±(0.25%FS + 1 digit)
0 ~ 24 mA	0.1 mA	±(0.5%FS + 1 digit)

The above spec. accuracy tested under the environment RF field strength of less than 3 V/M and frequency of less than 30 MHz only

DISCLAIMER
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Hisham Odeh	11/15/00
CHECKED BY:	DATE:
JOHN COLE	11/21/00
APPROVED BY:	DATE:
Daniel Carey	11/21/00

TENMA®

DRAWING TITLE: **Current Calibrator**

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	72-6694	95B8302.dwg	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1

