Application Instructions Statguard® Dissipative Neutral Floor Cleaner





Item No. 71045, 10 litres

Description

Charleswater's Statguard® Dissipative Floor Cleaner is specifically formulated to clean floors treated with Statguard® Dissipative Floor Finish. Statquard® Floor Cleaner is formulated with dissipative agents that will rejuvenate and improve the static dissipative properties of Statguard® Floor Finish, as well as other dissipative or conductive floor tiles and polymer type floor finishes. Charleswater's Dissipative Cleaner effectively cleans without leaving behind any harmful residue that can dull the surface or impede dissipation properties. This product is also recommended for use on conductive floor tile.

Application

Charleswater's Statguard® Floor Cleaner can be used on other floors and finishes. It is ideal for cleaning dissipative or conductive floor tiles as well as Statguard® finishes. The floor cleaner is more agressive than a damp mop (diluted finish and water or plain water) and does take the gloss down a bit as it cleans the surface. We suggest you first try a small area for compatibility.

Heavy to moderate traffic floors can be cleaned once a week. Light traffic floors can be cleaned 2 to 3 times a month or as needed.

EQUIPMENT NEEDED:

- Push broom
- · Clean and untreated mop
- Buckets
- Statguard[®] Dissipative Cleaner
- 1. Push broom the surface to be cleaned.
- Dilute Statguard[®] Dissipative Cleaner 19 litres of clean water to 1.9 litres of cleaner concentrate.
- Thoroughly mix the cleaner solution before application. Use a clean untreated mop to damp mop the area. Wring out excess fluid and do not flood a treated floor with water. Do not use a scrubbing machine to clean the floor.
- 4. Allow 30 to 60 minutes drying time before walking on the cleaned area.

Clean floors treated with Statguard® Floor Finish using Statguard® Cleaner. Do not damp mop with high alkaline or high residue cleaner. Using harsh detergents can damage a treated floor's static dissipative properties.

Physical Properties

Total Solids: 15%

Coverage: 500 sq.metres/

litre of concentrate

pH Value: 7.0

Colour: Green

Odour: Floral

Freeze/Thaw Passes three

Stability: cycles

Drying Time: 30 - 60 min.

@ 55% RH

Surface Resistivity: 106 - 109 Ohms

per ASTM D257

@ 100V

NOTE: Statguard® Dissipative Floor Cleaner does not have a set life span. The chemicals are not known to degrade over time when stored at the proper temperature conditions as stated in the Material Safety Data Sheet. We also recommend that the product be stored in its original container and be sealed when not in use.

Statguard[®] Dissipative Floor Cleaner is listed with the number UBA 50550001 by the German Umweltbundesamt.

Limited Warranty

Charleswater expressly warrants that for a period of one (1) year from the date of purchase, Charleswater's Statguard[®]
Dissipative Floor Cleaner will be free of defects in material. Within the warranty period, the material will be replaced, free of charge. Call customer service at 00 44 (0) 1892-665313 for a Return Material Authorisation (RMA) and proper shipping instructions and address. You should include a copy of your original packing slip, invoice, or other proof of purchase date. Any material under warranty should be shipped prepaid to the Charleswater factory in Crowborough, UK. Warranty replacements will take approximately two weeks.

Warranty Exclusions

THE FOREGOING EXPRESS WARRANTY IS MADE IN LIEU OF ALL OTHER PRODUCT WARRANTIES, EXPRESSED AND IMPLIED, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE WHICH ARE SPECIFICALLY DISCLAIMED. The express warranty will not apply to defects or damage due to accidents, neglect, misuse, alterations, operator error, or failure to properly maintain, clean or repair products.

Limit of Liability

In no event will Charleswater or any seller be responsible or liable for any injury, loss or damage, direct or consequential, arising out of the use of or the inability to use the product. Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith.

Unit 17. Millbrook Business Park, Sybron Way • Crowborough, East Sussex TN6 3JZ United Kingdom Phone: 00 44 (0) 1892-665313, Fax: 00 44 (0) 1892-668838 • E-mail: info@charleswater.co.uk, Internet: www.charleswater.co.uk

EC-Material Safety Data Sheet, according to 91/155EC

Date: March 6, 2008

STATGUARD® FLOOR CLEANER

1. IDENTIFICATION OF THE PRODUCT AND OF THE ENTERPRISE

Chemical name: Cleaner, Floor

Manufacturer Desco Industries, Inc. Charleswater

> 90 Hudson Road Unit 17. Millbrook Business Park, Sybron Way

Crowborough, East Sussex TN 3JZ Canton, MA 02021

U.S.A. United Kingdom

Phone: (781) 821-8370 Phone: 00 44 (0) 1892-665313 **Emergency**

(781) 575-0172 00 44 (0) 1892-668838 Fax: Fax:

2. INFORMATION ON INGREDIENTS/COMPOSITION

Weight CAS-No. **TLV-value R-Phrases** 400ppm Isopropanol* <1% 67-63-0 R11, R36, R67

*These items are listed on the SARA Title III Section 313 Inventory

HMIS RATING: 0 Health 1 Reactivity Flammability 0 Personal Protection В

3. HAZARDS IDENTIFICATION

A high concentration of liquid, mist, or vapour may cause irritation or permanent injury. Eves

Skin Repeated or continuous contact may cause irritation of the skin, an allergic reaction, or aggravate existing

dermatitis.

Pain. discomfort in the mouth, chest, dizziness. Ingestion Inhalation Irritation of nose and throat, discomfort and coughing.

4. FIRST AID MEASURES

Eve Contact Flush with water for at least 15 minutes.

Skin Contact Wash with soap and water.

DO NOT induce vomiting, may cause damage to mouth, throat, or esophagus. Contact a physician. Ingestion

Inhalation Move subject to fresh air.

5. EXTINGUISHING MEASURES

Proper Extinguishing Media Not Applicable

Protective Clothing Wear appropriate protective clothing

6. MEASURES TO EXPOSURE OF PRODUCT

Personal Precautions Wearing protective clothing. Wear proper eye protection. Extinguish all ignition sources. Keep spills and cleaning runoffs out of municipal sewers and open bodies of water. **Environmental Precautions**

Cleaning Procedures For discard incinerate the solids and the contaminated diking material according to local, state, and federal

regulations.

7. HANDLING AND STORAGE

Use in well-ventilated areas; avoid breathing vapours. Keep containers closed when not in use. Avoid freezing. Handling Storage

Storage Temperature: Max. 49°C/120°F - 1°C/34°F. Keep from freezing.

8. EXPOSURE CONTROL/PERSONAL EXPOSURE

TLV-value 400ppm maximum for Isopropanol Control Parameters

Other Regulations None

Measures For Technical Control Preferences of technical measure to prevent or control contact with the product. Isolating process and

personnel, mechanical ventilation (dilution and local exhaust) and the regulation of process conditions. In case

© 2008 Charleswater Ltd.

of non-prevention or non-control, proper protective wearing should be used.

Respiratory Protection Wear MSHA/NIOSH approved respirator where exposure limits are exceeded.

Hand Protection Impervious/Neoprene Gloves

Eye Protection Chemical Splash Goggles (ANSI Z-87.1).

Work/Hygienic Practices Wash hands before eating, smoking, or using washroom facilities.

9. PHYSICAL AND CHEMICAL PROPERTIES

Form Liquid

Colour Clear, green liquid Smell Mild floral aroma

pH 7.0

Boiling Point at °C 212°F (100°C)

Melting Point at °C 0°C

Flash Point at °C Noncombustible

Inflammability Limits N/A

(vol.% in air)

Solubility in water Soluble Vapour Pressure (mmHG) NA Vapour Density (air = 1) NA Density at 20° C NA Specific Gravity (H20 = 1) 1.0 - 1.2

Inflammability Classification according to EC-regulations "non-flammable".

Ignition Temperature NA
Evaporation Rate NA

10. STABILITY AND REACTIVITY

Stability/Reactivity Stable product at normal conditions.

Conditions to avoid Temperatures above 49°C/120°F and below 1°C/34°F.

Materials to avoid Avoid contamination with strong acids and oxidizing agents.

Hazardous Decomposition Thermal decomposition may yield carbon monoxide.

11. TOXICOLOGICAL INFORMATION

All information refers to the main component Isopropanol.

Acute toxicity None known Special Effects None known

12. ECOLOGICAL INFORMATION

No environmental hazards have been reported or known.

Mobility The product is aqueous and will be separated in aqueous conditions.

Degradability NA
Bioaccumulation Not likely
Ecotoxicity None known

Reference to BimSchV NA

Hazard Classification None Hazardous

13. DISPOSAL CONSIDERATIONS

Product Coagulate the emulsion by the stepwise of Ferric Chloride and Lime. Incinerate the solids and the

contaminated diking material according to local, state, and federal regulations.

Hazardous Waste Number Nonregulated

14. TRANSPORT INFORMATION

This product is not classified for transport under ADR/IMDG regulations.

15. REGULATORY INFORMATION

Physical/Chemical Indication Non-flammable

Risk-phrase (R11): Highly flammable. (R36/38): irritates eyes and skin. (R67): Vapors may cause drowsiness and dizziness. Safety Phrase (S2): keep away from children, (S7): keep containers well closed, (S16): Keep away from sources of ignition -

No smoking. (S24/25): avoid contact with skin and eyes, (S26): In case of contact with eyes, rinse immediately

with plenty of water and seek medical advice.

EU Classification This product does not have to be classified according to the EU Regulations.

(67/548/EEC-88/379/EEC)

EINECS Status All components are included in the EINECS Inventories.

16. OTHER INFORMATION

Further Information None

Disclaimer

The information given in this publication has been worked up to the best of the knowledge of Charleswater, as well as taking into consideration the applicable laws and regulations. We cannot anticipate all conditions under which this information and our products or the products of the manufacturers in combination with our products may be used. We accept no responsibility for the results obtained by the application information or the safety and suitability of our product or combination with other products. Users are advised to make their own tests to determine the safety and suitability of each such product or product combination for their own purposes. Unless otherwise agreed in writing, we sell the products without warranty, and buyers and end users assume responsibility and liability for loss or damage arising from the handling and use of our products, whether used alone or in combination with other products.