

## Fusible, Non-Flammable Resistors



### FEATURES

- Overload protection without risk of fire
- Wide range of overload currents.

### APPLICATIONS

- Audio
- Video.

A homogeneous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with a grey, flame retardant lacquer which provides

electrical, mechanical, and climatic protection. The encapsulation is resistant to all cleaning solvents in accordance with "MIL-STD-202E, method 215", and "IEC 60068-2-45".

TECHNICAL SPECIFICATIONS		
DESCRIPTION	VALUE	
	NFR25	NFR25H
Resistance range <sup>(1)</sup>	0.22 Ω to 15 kΩ	
Resistance tolerance and series	± 5 %; E24 series	
Maximum dissipation at T <sub>amb</sub> = 70 °C	0.33 W	0.5 W
Thermal resistance R <sub>th</sub>	240 K/W	150 K/W
Temperature coefficient:		
0.22 Ω ≤ R ≤ 4.7 Ω	≤ ± 200 × 10 <sup>-6</sup> /K	≤ ± 200 × 10 <sup>-6</sup> /K
4.7 Ω < R ≤ 15 Ω	≤ ± 200 × 10 <sup>-6</sup> /K	≤ ± 100 × 10 <sup>-6</sup> /K
15 Ω < R ≤ 15 kΩ	≤ ± 100 × 10 <sup>-6</sup> /K	≤ ± 100 × 10 <sup>-6</sup> /K
Maximum permissible voltage (DC or RMS)	250 V	350 V
Basic specifications	IEC 60115-1 and 60115-2	
Climatic category (IEC 60068)	55/155/56	
Stability after:		
load	ΔR/R max.: ± 1 % + 0.05 Ω	
climatic tests	ΔR/R max.: ± 1 % + 0.05 Ω	
soldering	ΔR/R max.: ± 0.25 % + 0.05 Ω	

#### Note

1. Ohmic values (other than resistance range) are available on request.

12NC ORDERING CODE INDICATING RESISTOR TYPE AND PACKAGING				
TYPE	ORDERING CODE 23... ..			
	BANDOLIER IN AMMOPACK			BANDOLIER ON REEL
	RADIAL TAPED	STRAIGHT LEADS		STRAIGHT LEADS
	4000 units	1000 units	5000 units	5000 units
NFR25	06 204 03...	22 205 13...	22 205 33...	22 205 23...
NFR25H	06 207 03...	22 207 13...	22 207 33...	22 207 23...

## ORDERING INFORMATION

### Numeric Ordering Code (12NC)

- The resistors have a 12-digit ordering code starting with 23
- The subsequent 7 digits indicate the resistor type and packaging.
- The remaining 3 digits indicate the resistance values:
  - The first 2 digits indicate the resistance value.
  - The last digit indicates the resistance decade.


### Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
0.22 to 0.91 $\Omega$	7
1 to 9.1 $\Omega$	8
10 to 91 $\Omega$	9
100 to 910 $\Omega$	1
1 to 9.1 k $\Omega$	2
10 to 15 k $\Omega$	3

### Ordering Example

The ordering code for a NFR25 resistor with value 750  $\Omega$ , supplied on a bandolier of 1000 units in ammpack is: 2322 205 13751.

## DIMENSIONS



DIMENSIONS - resistor types and relevant physical dimensions				
TYPE	ØD MAX.	L <sub>1</sub> MAX.	L <sub>2</sub> MAX.	Ød
NFR25	2.5	6.5	7.5	0.58 ±0.05
NFR25H				

MASS PER 100 UNITS	
TYPE	MASS (g)
NFR25	21
NFR25H	22

For ease of recognition a fifth ring is added, which is violet for type NFR25 and white for type NFR25H.

### OUTLINES

The length of the body ( $L_1$ ) is measured by inserting the leads into holes of two identical gauge plates and moving these plates parallel to each other until the resistor body is clamped without deformation ("IEC publication 60294").

## MARKING

The nominal resistance and tolerance are marked on the resistor using four coloured bands in accordance with IEC publication 60062 "Colour codes for fixed resistors".

## FUNCTIONAL PERFORMANCE

### PRODUCT CHARACTERIZATION

Standard values of nominal resistance are taken from the E24 series for resistors with a tolerance of  $\pm 5\%$ . The values of the E24 series are in accordance with "IEC publication 60063".


LIMITING VALUES		
TYPE	LIMITING VOLTAGE <sup>(1)</sup> (V)	LIMITING POWER (W)
NFR25	250	0.33
NFR25H	350	0.5

### Note

1. The maximum voltage that may be continuously applied to the resistor element, see "IEC publication 60115-1". The maximum permissible hot-spot temperature is 155 °C.



The power that the resistor can dissipate depends on the operating temperature.




Maximum dissipation ( $P_{max}$ ) in percentage of rated power as a function of the ambient temperature ( $T_{amb}$ ).


**Derating**

The resistors will fuse without the risk of fire and within an indicated range of overload. Fusing means that the resistive value of the resistor increases at least 100 times.


The fusing characteristic is measured under constant voltage.




**NFR25** This graph is based on measured data which may deviate according to the application. Fusing Characteristics:  $\leq 1 \Omega$ .




**NFR25** This graph is based on measured data which may deviate according to the application. Fusing Characteristics:  $1 \Omega \leq R \leq 15 \Omega$ .



**NFR25** This graph is based on measured data which may deviate according to the application. Fusing Characteristics:  $15 \Omega \leq R \leq 15 \Omega$ .




**NFR25H** This graph is based on measured data which may deviate according to the application. Fusing Characteristics:  $\leq 1 \Omega$ .




**NFR25H** This graph is based on measured data which may deviate according to the application. Fusing Characteristic.


**Fusing Characteristic**



NFR25 Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max}$ ) as a function of pulse duration ( $t_i$ ),  $0.22 \Omega \leq R < 15 \Omega$ .




NFR25 Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max}$ ) as a function of pulse duration ( $t_i$ ),  $15 \Omega < R \leq 15 k\Omega$ .




NFR25 Pulse on a regular basis; maximum permissible peak pulse voltage ( $\hat{V}_{max}$ ) as a function of pulse duration ( $t_i$ ).

Pulse Loading Capabilities




NFR25H Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max}$ ) as a function of pulse duration ( $t_i$ ).




NFR25H Pulse on a regular basis; maximum permissible peak pulse voltage ( $\hat{V}_{max}$ ) as a function of pulse duration ( $t_i$ ).

**Pulse Loading Capabilities**




NFR25 Hot-spot temperature rise ( $\Delta T$ ) as a function of dissipated power.

**Application Information**




Minimum distance from resistor body to PCB = 1 mm.

**NFR25** Temperature rise ( $\Delta T$ ) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting.



**NFR25H** Hot-spot temperature rise ( $\Delta T$ ) as a function of dissipated power.



Minimum distance from resistor body to PCB = 1 mm.

**NFR25H** Temperature rise ( $\Delta T$ ) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting.

**Application Information**



**TESTS AND REQUIREMENTS**

Essentially all tests are carried out in accordance with the schedule of "IEC publication 60115-1", category LCT/UCT/56 (rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days). The testing also covers the requirements specified by EIA and EIAJ.

The tests are carried out in accordance with IEC publication 60068-2, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to "IEC 60068-1", subclause 5.3.

In the Test Procedures and Requirements table the tests and requirements are listed with reference to the relevant clauses of "IEC publications 60115-1 and 60068-2"; a short description of the test procedure is also given. In some instances deviations from the IEC recommendations were necessary for our method of specifying. For inflammability requirements reference is made to "IEC 60115-1" and to "EN 140000, appendix D".

All soldering tests are performed with mildly activated flux.

<b>TEST PROCEDURES AND REQUIREMENTS</b>					
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS	
				NFR25	NFR25H
<b>TESTS IN ACCORDANCE WITH THE SCHEDULE OF IEC PUBLICATION 60115-8</b>					
4.4.1		visual examination		no holes; clean surface; no damage	
4.4.2		dimensions (outline)	gauge (mm)	see Dimensions Table	
4.5		resistance	applied voltage (+ 0/-10 %): R < 10 Ω: 0.1 V 10 Ω ≤ R < 100 Ω: 0.3 V 100 Ω ≤ R < 1 kΩ: 1 V 1 kΩ ≤ R < 10 kΩ: 3 V 10 kΩ ≤ R ≤ 15 kΩ: 10 V	R - R <sub>nom</sub> : max. ± 5 %	
4.18	20 (Tb)	resistance to soldering heat	thermal shock: 3 s; 350 °C; 3 mm from body	ΔR/R max.: ± 0.25 % + 0.05 Ω	
4.29	45 (Xa)	component solvent resistance	isopropyl alcohol or H <sub>2</sub> O followed by brushing in accordance with "MIL 202 F"	no visual damage	
4.17	20 (Ta)	solderability	2 s; 235 °C	good tinning; no damage	
4.7		voltage proof on insulation	500 V (RMS) during 1 minute; metal block method	no breakdown or flashover	
4.16	21 (U)	robustness of terminations:			
4.16.2	21 (Ua1)	tensile all samples	load 10 N; 10 s	number of failures < 10 × 10 <sup>-6</sup>	
4.16.3	21 (Ub)	bending half number of samples	load 5 N; 4 × 90°	number of failures < 10 × 10 <sup>-6</sup>	
4.16.4	21 (Uc)	torsion other half of samples	3 × 360° in opposite directions	no damage ΔR/R max.: ± 0.25 % + 0.05 Ω	
4.20	29 (Eb)	bump	3 × 1500 bumps in 3 directions; 40 g	no damage ΔR/R max.: ± 0.25 % + 0.05 Ω	
4.22	6 (Fc)	vibration	frequency 10 to 500 Hz; displacement 1.5 mm or acceleration 10 g; 3 directions; total 6 hours (3 × 2 hours)	no damage ΔR/R max.: ± 0.25 % + 0.05 Ω	
4.19	14 (Na)	rapid change of temperature	30 minutes at LCT and 30 minutes at UCT; 5 cycles	no visual damage ΔR/R max.: ± 0.25 % + 0.05 Ω	
4.23		climatic sequence:			
4.23.3	30 (Db)	damp heat (accelerated) 1 <sup>st</sup> cycle			
4.23.6	30 (Db)	damp heat (accelerated) remaining cycles	6 days; 55 °C; 95 to 98 % RH	R <sub>ins</sub> min.: 10 <sup>3</sup> MΩ ΔR/R max.: ± 1 % + 0.05 Ω	



TEST PROCEDURES AND REQUIREMENTS					
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS	
				NFR25	NFR25H
4.24.2	3 (Ca)	damp heat (steady state) (IEC)	56 days; 40 °C; 90 to 95% RH; loaded with 0.01 P <sub>n</sub> (IEC steps: 4 to 100 V)	R <sub>ins</sub> max.: 1 000 MΩ ΔR/R max.: ± 1 % + 0.05 Ω	
4.25.1		endurance (at 70 °C)	1 000 hours; loaded with P <sub>n</sub> or V <sub>max</sub> ; 1.5 hours on and 0.5 hours off	ΔR/R max.: ± 1 % + 0.05 Ω	
4.25.3		endurance at upper category temperature	1 000 hours; no load	ΔR/R max.: ± 1 % + 0.05 Ω	
4.8.4.2		temperature coefficient	at 20/LCT/20 °C and 20/UCT/20 °C (TC × 10 <sup>-6</sup> /K): 0.22 Ω ≤ R ≤ 4.7 Ω 4.7 Ω < R ≤ 15 Ω 15 Ω < R ≤ 15 kΩ	≤ ± 200 × 10 <sup>-6</sup> /K ≤ ± 200 × 10 <sup>-6</sup> /K ≤ ± 100 × 10 <sup>-6</sup> /K	≤ ± 200 × 10 <sup>-6</sup> /K ≤ ± 100 × 10 <sup>-6</sup> /K ≤ ± 100 × 10 <sup>-6</sup> /K
4.12		noise	"IEC publication 60195"	< 0.1 μV/V	
4.26		accidental overload	cheese-cloth	nonflammable	
OTHER TESTS IN ACCORDANCE WITH IEC 60115 CLAUSES AND IEC 60068 TEST METHOD					
4.17	20 (Ta)	solderability (after ageing)	8 hours steam or 16 hours 155 °C; leads immersed 6 mm for 2 ± 0.5 s in a solder bath at 235 ± 5 °C	good tinning (≥ 95 % covered); no damage	
4.6.1.1		insulation resistance	maximum voltage 500 V (DC) after 1 minute; metal block method	R <sub>ins</sub> min.: 10 <sup>4</sup> MΩ	
see 2 <sup>nd</sup> amendment to "IEC 60115-1", Jan:'87		pulse load		see the Pulse Loading Capabilities graphs	