

### General description

A translucent PVC repair tape coated with a clear, pressure sensitive adhesive.

- Easy unwind
- Flexible
- Conformable to awkward shapes
- Water resistant
- Good abrasion resistance
- Non-corrosive adhesive
- UV resistant

### Specifications

Certification\* to the BS3887 : 1991 standard is available on request.

### Technical Details

#### Typical values

Thickness	0.15mm
Breaking Load	26 N/cm
Elongation	130%
Adhesion	
Steel	3.5 N/cm
Self	2.8 N/cm
Copper Corrosion	No Staining
Flame Retardancy	Self extinguishing
RoHS Compliant	Yes
Service Temperature	0°C to +70°C
Application Temperature	+5°C to +40°C
Storage Temperature	+12°C to +25°C

\*Standard charge for certificate: £25.00.



#### NOTE

Except where indicated otherwise, the figures stated are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

#### STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

 **ADVANCE**  
adhesive tapes



BS EN ISO 9001  
Q05206



INVESTOR IN PEOPLE

Advance Tapes International Limited, PO Box 122,  
Abbey Meadows, Leicester, LE4 5RA.

Tel: 0116 251 0191. Fax: 0116 265 2046. [www.advancetapes.com](http://www.advancetapes.com)

#### AFERA

Association des Fabricants Européens de  
Rubans Auto-Adhésifs.