

01

01 Combination Pliers, Chrome Vanadium

DIN ISO 5746



01 06 190

- ▶ for heaviest duty
- ▶ with gripping zones for flat and round material, suitable for versatile use
- ▶ with cutting edges for soft, hard and piano wire
- ▶ long cutting edges for thicker cables
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- ▶ particularly wear resistant gripping jaws due to additional hardening; hardness of the gripping jaws approx. 53 HRC
- ▶ Chrome Vanadium electric steel, oil-hardened and tempered

| Article-No. | EAN-Code | Head | Handles | Cutting capacities | | | | g |
|-------------|----------|---------------|--------------------------------------------------|--------------------|------|------|-----------------|-----|
| | | | | Ø mm | Ø mm | Ø mm | mm ² | |
| 01 06 160 | 040729 | chrome plated | insulated with two-colour dual component handles | 2.0 | 1.5 | 10.0 | 16.0 | 210 |
| 190 | 040415 | chrome plated | 1000 V VDE-tested | 2.5 | 2.0 | 13.0 | 25.0 | 300 |

08

08 Small Combination Pliers



08 05 110

- ▶ compact combination pliers for professionals and hobbyists
- ▶ with gripping zones for flat and round material, suitable for versatile use
- ▶ with cutting edges for soft and hard wire
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- ▶ Vanadium steel, oil-hardened and tempered
- Model 08 15 110:**
 - ▶ with leather pouch; a special gift

| Article-No. | EAN-Code | Head | Handles | Cutting capacities | | | | g |
|-------------|----------|---------------|------------------------------------------------------------|--------------------|------|------|-----------------|-----|
| | | | | Ø mm | Ø mm | Ø mm | mm ² | |
| 08 05 110 | 034957 | chrome plated | with two-colour dual component handles | 2.5 | 1.6 | 9.0 | 10.0 | 90 |
| 08 15 110 | 015390 | chrome plated | with two-colour dual component handles, with leather pouch | 2.5 | 1.6 | 9.0 | 10.0 | 100 |