

DC Axial Fans Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to show all details.

24 10 M L - 04 W - B 1 0 - X 00
 (1) (2) (3) (4) (5) (6) (7) (8) (9) (10) (11)

Display All

<table border="1"> <thead> <tr> <th>1. Size</th> <th>2. Thickness</th> </tr> </thead> <tbody> <tr><td>10 25mm 28 70mm</td><td>04 10mm</td></tr> <tr><td>12 30mm 31 80mm</td><td>06 15mm</td></tr> <tr><td>14 35mm 36 92mm</td><td>08 20mm</td></tr> <tr><td>16 40mm 47 119mm</td><td>10 25mm</td></tr> <tr><td>20 50mm 50 127mm</td><td>12 32mm</td></tr> <tr><td>21 52mm 59 150mm</td><td>15 38mm</td></tr> <tr><td>24 60mm 68 172mm</td><td>20 50mm</td></tr> </tbody> </table>	1. Size	2. Thickness	10 25mm 28 70mm	04 10mm	12 30mm 31 80mm	06 15mm	14 35mm 36 92mm	08 20mm	16 40mm 47 119mm	10 25mm	20 50mm 50 127mm	12 32mm	21 52mm 59 150mm	15 38mm	24 60mm 68 172mm	20 50mm	<table border="1"> <thead> <tr> <th>3. Series</th> <th>5. Input Voltage</th> </tr> </thead> <tbody> <tr><td>P Series</td><td>S Series 01 5V 06 36V</td></tr> <tr><td>M Series</td><td>F Series 02 6V 07 48V</td></tr> <tr><td>N Series</td><td>03 9V 09 Custom voltage</td></tr> <tr><td>K Series</td><td>04 12V</td></tr> <tr><td>H Series</td><td>05 24V</td></tr> </tbody> </table>	3. Series	5. Input Voltage	P Series	S Series 01 5V 06 36V	M Series	F Series 02 6V 07 48V	N Series	03 9V 09 Custom voltage	K Series	04 12V	H Series	05 24V	<table border="1"> <thead> <tr> <th>4. Function</th> <th>7. Bearing</th> <th>6. Termination</th> <th>8. Speed</th> </tr> </thead> <tbody> <tr><td>Brushless Type</td><td>B Ball Bearing</td><td>w Lead Wires</td><td>1<2<3<4<5<6<7<8</td></tr> <tr><td>DCM</td><td>S Sleeve Bearing</td><td>T Terminal Type</td><td>low high</td></tr> </tbody> </table>	4. Function	7. Bearing	6. Termination	8. Speed	Brushless Type	B Ball Bearing	w Lead Wires	1<2<3<4<5<6<7<8	DCM	S Sleeve Bearing	T Terminal Type	low high																	
1. Size	2. Thickness																																																										
10 25mm 28 70mm	04 10mm																																																										
12 30mm 31 80mm	06 15mm																																																										
14 35mm 36 92mm	08 20mm																																																										
16 40mm 47 119mm	10 25mm																																																										
20 50mm 50 127mm	12 32mm																																																										
21 52mm 59 150mm	15 38mm																																																										
24 60mm 68 172mm	20 50mm																																																										
3. Series	5. Input Voltage																																																										
P Series	S Series 01 5V 06 36V																																																										
M Series	F Series 02 6V 07 48V																																																										
N Series	03 9V 09 Custom voltage																																																										
K Series	04 12V																																																										
H Series	05 24V																																																										
4. Function	7. Bearing	6. Termination	8. Speed																																																								
Brushless Type	B Ball Bearing	w Lead Wires	1<2<3<4<5<6<7<8																																																								
DCM	S Sleeve Bearing	T Terminal Type	low high																																																								
<table border="1"> <thead> <tr> <th>4. Motor Function</th> </tr> </thead> <tbody> <tr><td>Brushless Type DCM</td></tr> </tbody> </table>	4. Motor Function	Brushless Type DCM																																																									
4. Motor Function																																																											
Brushless Type DCM																																																											
<table border="1"> <thead> <tr> <th>10. Special Control Function</th> <th>11. Individual Specifications</th> </tr> </thead> <tbody> <tr><td>0 Standard type</td><td>Standard Type</td></tr> <tr><td>9 Sensor type</td><td>00 Standard</td></tr> <tr><td>3 2-speed type</td><td>01-99 Custom</td></tr> <tr><td>7 Temperature detecting variable speed type/PWM control type</td><td>00 Sensor Type</td></tr> <tr><td>6 Temperature detecting variable speed type/Sensor type</td><td>00 Locked Rotor Alarm Signal(Standard)</td></tr> <tr><td>5 2-speed type / Sensor type</td><td>01-49 Locked Rotor Alarm Signal(Custom)</td></tr> <tr><td></td><td>50 Tachometer Signal (Standard)</td></tr> <tr><td></td><td>51-99 Tachometer Signal (Custom)</td></tr> </tbody> </table> <table border="1"> <thead> <tr> <th>Item</th> <th>Classification</th> <th>Mounting Style</th> </tr> </thead> <tbody> <tr><td>L</td><td>Standard Model</td><td>Rib Type</td></tr> <tr><td>P</td><td>Standard Model</td><td>Flange Type</td></tr> <tr><td>B</td><td>Standard Model</td><td>Rib Type</td></tr> <tr><td>E</td><td>Standard Model</td><td>Flange Type</td></tr> <tr><td>G</td><td>Standard Model</td><td>Rib Type</td></tr> <tr><td>D</td><td>Standard Model</td><td>Flange Type</td></tr> <tr><td>T</td><td>Value Model</td><td>Rib Type</td></tr> <tr><td>S</td><td>Value Model</td><td>Flange Type</td></tr> <tr><td>C</td><td>Value Model</td><td>Rib Type</td></tr> <tr><td>F</td><td>Value Model</td><td>Flange Type</td></tr> <tr><td>J</td><td>Value Model</td><td>One Side Rib Type</td></tr> <tr><td>H</td><td>Value Model</td><td>One Side Flange Type</td></tr> </tbody> </table>	10. Special Control Function	11. Individual Specifications	0 Standard type	Standard Type	9 Sensor type	00 Standard	3 2-speed type	01-99 Custom	7 Temperature detecting variable speed type/PWM control type	00 Sensor Type	6 Temperature detecting variable speed type/Sensor type	00 Locked Rotor Alarm Signal(Standard)	5 2-speed type / Sensor type	01-49 Locked Rotor Alarm Signal(Custom)		50 Tachometer Signal (Standard)		51-99 Tachometer Signal (Custom)	Item	Classification	Mounting Style	L	Standard Model	Rib Type	P	Standard Model	Flange Type	B	Standard Model	Rib Type	E	Standard Model	Flange Type	G	Standard Model	Rib Type	D	Standard Model	Flange Type	T	Value Model	Rib Type	S	Value Model	Flange Type	C	Value Model	Rib Type	F	Value Model	Flange Type	J	Value Model	One Side Rib Type	H	Value Model	One Side Flange Type		
10. Special Control Function	11. Individual Specifications																																																										
0 Standard type	Standard Type																																																										
9 Sensor type	00 Standard																																																										
3 2-speed type	01-99 Custom																																																										
7 Temperature detecting variable speed type/PWM control type	00 Sensor Type																																																										
6 Temperature detecting variable speed type/Sensor type	00 Locked Rotor Alarm Signal(Standard)																																																										
5 2-speed type / Sensor type	01-49 Locked Rotor Alarm Signal(Custom)																																																										
	50 Tachometer Signal (Standard)																																																										
	51-99 Tachometer Signal (Custom)																																																										
Item	Classification	Mounting Style																																																									
L	Standard Model	Rib Type																																																									
P	Standard Model	Flange Type																																																									
B	Standard Model	Rib Type																																																									
E	Standard Model	Flange Type																																																									
G	Standard Model	Rib Type																																																									
D	Standard Model	Flange Type																																																									
T	Value Model	Rib Type																																																									
S	Value Model	Flange Type																																																									
C	Value Model	Rib Type																																																									
F	Value Model	Flange Type																																																									
J	Value Model	One Side Rib Type																																																									
H	Value Model	One Side Flange Type																																																									

M	Value Model	Rib Type
V	Value Model	Flange Type
X	Vented casing	Flange Type

10. Product No.

Item	Classification	Mounting Style	Item	Classification	Mounting Style	Item	Classification	Mounting Style
L	Standard Model	Rib Type	D	Standard Model	Flange Type	J	Value Model	One Side Rib Type
P	Standard Model	Flange Type	T	Value Model	Rib Type	H	Value Model	One Side Flange Type
B	Standard Model	Rib Type	S	Value Model	Flange Type	M	Value Model	Rib Type
E	Standard Model	Flange Type	C	Value Model	Rib Type	V	Value Model	Flange Type
G	Standard Model	Rib Type	F	Value Model	Flange Type	X	Vented casing	Flange Type