

95

95 Shears for KEVLAR® Fibres



95 03 160 SB

- ▶ only for cutting fibres of KEVLAR® in optical fibre cables, not recommended for other materials
- ▶ precision grinding with serration prevents the fibres from slipping and guarantees a clean cut
- ▶ riveted precision joint, for low-friction movement and smooth and even cutting of the thin KEVLAR® fibres
- ▶ hard-chrome plated, ground surface
- ▶ user-friendly plastic handles
- ▶ body of shears oil-hardened and tempered

Article-No.	EAN-	Head	Handles	
Length	Code			♻
mm	4003773-			g
95 03 160 SB	043362	chrome plated	plastic coated	80



Precision ground with fine toothing for clean, non-slip (nonskid) cut

95

95 Combination Shears



95 05 140



95 05 185



95 05 190

- ▶ combination shears for cutting cardboard, plastics, aluminium, brass and copper foils
- ▶ **not suitable for steel wire or iron sheets**
- ▶ precision ground, hardened blades
- ▶ with opening spring and locking device
- ▶ with guard
- ▶ adjustable screw joint
- ▶ blades made of stainless steel
- ▶ oil-hardened and tempered

Model 95 05 185:

- ▶ angled shape - for easy execution of long cuttings
- ▶ ergonomically shaped plastic handles

Article-No.	EAN-	Head	Handles	
Length	Code			♻
mm	4003773-			g
95 05 140	019589	bright polished	with plastic handles	50
165	060277			110
190	019602			120

KEVLAR® is a registered Trademark of E. I. du Pont de Nemours and Company