

CT-570 The difference is it's built like a carthorse and behaves like a thoroughbred


The 570 series has become the popular contractors' extraction cleaner by choice and this is not by chance... but by design.

"Built like a carthorse" it really is, with the full Structofoam construction designed to take the bangs and bruises that any machine will suffer in true commercial use because that's what you need – a machine that's construction is beyond reproach and will give you reliable service.


When it comes to performance, this is where the thoroughbred element of design becomes so apparent. In the 570 range you have the CT-570 simplex one-motored, or CTD-572 duplex two-motored specification. They all incorporate a Powerflo® pump system ensuring that cleaning solution can be injected deep into the carpet fabric and yet fully extracted to ensure a continuous deep cleaning cycle. The duplex 572 model also incorporates a 2-stage Hi/Lo feature ensuring a power and performance choice to suit varying requirements.

The standard cleaning accessories are also to full commercial specification throughout, incorporating extra-long vacuum hoses, stainless steel tubesets, die-cast aluminium extraction nozzles and a fully professional upholstery nozzle that is also ideal for spot cleaning in emergencies, difficult-to-get-to areas, and also for the full valeting of vehicle interiors.

For those who want added scope, a dry filter and a few additional accessories will give you a full multipurpose system, coping with dry vacuuming and wet pick-up, in addition to the full extraction performance (Kit AA18).













Accessory Kit – AA14 (38mm/1 1/4")



Yes, the 570 is a real professional workhorse that will stay the course long after the others have gone.

TECHNICAL DATA

				
Motor	Power	Airflow	Suction	Capacity wet
CT-570: 1000W CTD-572: 2000W	230/120/100V AC 50/60Hz	43.5 litre/sec. 82.0 litre/sec	2450mm	23 litres
				
Capacity dry	Capacity injection	Cleaning Range	Weight	Size
15 litres	10/10	31.8m (104ft.)	15.5Kgs 18Kgs	415 x 415 x 615mm

Motor watts shown are the MAXIMUM input watts. The vacuum cleaner is designed to meet the requirements of the majority of international Approved Agencies, carrying labels on machines showing MEAN operational watts, being the full power watts consumed during normal use. e.g. 1000 watts MAX = 200 watts MEAN, 2000 watts MAX = 400 watts MEAN.

Numatic INTERNATIONAL

Distributed by:

231350/95011A



Numatic International Limited, Chard, Somerset, TA20 2LW

Tel: 01460 68480 Fax: 01460 68560

•Sales – Tel: 01460 68600 Fax: 01460 68458


Service-centre
handle

The Hi/Lo system for
Duplex models.




Cable storage
hook.


Cleaning solution
filter.



Full Structofoam Duplex
by-pass power head
and integrated
Powerflo' pump
system.




Float valve with
Safety net filter
(optional wet use)




Full Structofoam
one-piece container

Heavy duty
toggles.



Heavy duty castors



The dual clean and dirty
liquid containers and
safety float valve

2-Stage Filter system
(optional dry use).



2175