

SF 4240	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH			Connections	Resistor Value MΩ	Approvals		
			L1	L2	L3					
SF 4240-1/01	1	0.2mA	4.3	4.3	0.3	6.3 x 0.8 Faston	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
SF 4240-3/01	3	0.2mA	2.2	2.2	0.3	6.3 x 0.8 Faston	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
SF 4240-6/01	6	0.2mA	1.3	1.3	0.3	6.3 x 0.8 Faston	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
SF 4240-10/01	10	0.2mA	1.0	1.0	0.3	6.3 x 0.8 Faston	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
SF 4240-16/01	16	0.2mA	0.45	0.45	0.3	6.3 x 0.8 Faston	1	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>


**Temperature Range:** -25°C to +85°C  
**Operating Voltage:** 440/250Vac  
**Operating Frequency:** 0 to 400Hz  
**Test Voltage:** L+N to ground, 2700Vdc, 2 seconds

Approved  
 Submitted for Approval

### DIMENSIONS

All dimensions are nominal and in mm

IEC 950 (EN 60950 Applications)



### CIRCUIT DIAGRAM

