







The Optoelectronic Manufacturing Corporation



# 24V RGB Flexistrip™





## Technical Datasheet




RGB version of the popular Flexistrip™ range of high performance, extreme-versatility DC flexible LED strips designed for industrial, architectural, signage and many other illumination and lighting applications. Compatible with OMC's range of colour-change controllers.

### Key Features:

- Energy efficient 24V DC Design
- Industry leading LED density for RGB
- Compatible with wide range of colour-change controllers
- Compact, low profile and highly flexible
- Very high brightness
- Output characterised for lighting applications
- Up to 3 metres can be powered from one end
- Built-in antistatic protection
- Built-in reverse polarity protection
- Cut and link points regularly spaced along strip length
- Can be cut or joined end-to-end to form different lengths
- RoHS Compliant

### Typical Applications:

- Replacement of fluorescent light sources
- Built-up and flat-cut letter illumination
- Colour-changing light box illumination
- Accent lighting
- Colour-changing backlighting
- Lighting for machinery
- Colour-changing strip lights
- Furniture illumination
- Long-life alternative to neon
- Low energy lighting
- Lighting for point-of-sale applications
- Edge-illumination of acrylic lightguides
- Signalling and indication






**Typical electro-optical characteristics per channel at applied voltage = 24V DC and Ta=25°C**

Channel	LEDs per 200mm strip	Light output per 200mm strip	Beam angle 2θ½	Max current draw
Red	12 x Ultrabright Red Chips	7.1 lm	120°	40mA
Green	12 x Ultrabright Green Chips	29.5 lm	120°	40mA
Blue	12 x Ultrabright Blue Chips	9.2 lm	120°	40mA

Colours are for ease of reference only and do not indicate exact shade of LED output.

### Mechanical information

- ◆ Strip length 200mm
- ◆ Strip width 10mm
- ◆ Strip height 2.1mm
- ◆ 12 x 3 chip RGB LEDs per 200mm strip (180 chips per metre)
- ◆ Terminals are common anode as shown
- ◆ Note: Also available joined together in reels
- ◆ Cut/solder points every 6 LED packages (100mm)



(Dimensions in mm, tolerance ±0.5mm unless otherwise stated)

### Absolute maximum ratings (Ta=25°C where applicable)

Quantity	Rating
Applied Voltage to any Channel	24V DC
LED Reverse Voltage	5V
Operating Temperature Range	-35°C to +55°C
LED Forward Current	20mA
Temperature Range in Storage	-35°C to +100°C
Strip Forward DC Current	120mA



## **Application notes**

- ◆ Do not apply voltages greater than 24V DC to this product or damage may occur.
- ◆ Although electrostatic protection is built into this product, as with any semiconductor device it is recommended to avoid unnecessary electrostatic discharge.
- ◆ Connect anode to V solder pad, cathode to B (for blue channel), G (for green channel), R (for red channel) solder pads.
- ◆ For strip lengths greater than 3m, wiring in a "ring main" style configuration (i.e. a power feed at each end) is strongly recommended to reduce voltage drop. For very long lengths it is recommended to connect a power feed back to the supply after every 6m.
- ◆ Cut only at designated cut points. Do not cut between cut points as this will damage the product.
- ◆ Use of a regulated 24V DC supply is recommended.
- ◆ Do not expose to moisture unless product has been damp protected.
- ◆ Product may be fixed in place using double sided adhesive foam, hot glue or silicone.
- ◆ For soldering, use of a small 25W general purpose mains soldering iron is recommended, recommended soldering temperature is 260°C for maximum 5 seconds.
- ◆ When used in ambient temperatures greater than 25°C, please derate the drive current to ensure maximum reliability. Please contact us should you require a derating curve.

## **The Optoelectronic Manufacturing Corporation (UK) Ltd.**

Candela House,  
Cardrew Industrial Estate,  
Redruth,  
Cornwall  
TR15 1SS

Tel: 01209 215424

Fax: 01209 215197

General e-mail: [omc-sales@omc-uk.com](mailto:omc-sales@omc-uk.com)