# MC9S08QG8/4

Torget Applications		Features	Benefits
<ul> <li>&gt; Wireless sensor applications including SMAC</li> <li>&gt; Watchdog coprocessors</li> <li>&gt; Small appliances</li> <li>&gt; Handheld devices &gt; Secure boot coprocessors</li> <li>&gt; Security systems</li> </ul>		8-bit HCS08 Central Processor Unit (CPU)	
		> Up to 10 MHz (bus frequency) HCS08 CPU (central processor unit) at >2.1V operation for 100 ns minimum instruction time and 8 MHz bus frequency at <2.1V operation	<ul> <li>Offering high performance, even at low voltage levels for battery-operated applications</li> </ul>
		> HC08 instruction set with added BGND instruction	> Backward object-code compatibility with 68HC08 and 68HC05 so existing code libraries can still be used
			> Allows for efficient, compact module coding in assembly or C compiler
		> Support for up to 32 interrupt/reset sources	<ul> <li>Allows for software flexibility and optimization for real-time applications</li> </ul>
Overview		Integrated Third-Generation Flash Memory and RAM	
advantages of Freescale Semiconductor's HCS08	ends the	> Embedded Flash that is in-application reprogrammable over the full operating voltage and temperature range with a single power supply	<ul> <li>Provides users a single solution for multiple platforms or a single platform that is field reprogrammable in virtually any environment</li> </ul>
pin count, small-package microcontrollers. QG de	e 8-bit vices are low		> Does not require additional pin or power supply for Flash programming, simplifying the interface for in-line programming and allowing for more GPIO pins
voltage with on-chip in-c memory programmable c	circuit Flash down to 1.8V,	> Extremely fast, byte-writable programming; as fast as 20 us/byte	<ul> <li>&gt; Helps reduce production programming costs through ultra-fast programming, as well as lowering system power consumption due to shorter writes</li> </ul>
and afford the standard to of all HCS08 MCUs incl wait mode and multiple s	features luding stop modes.	> Up to 100,000 write/erase cycles at typical voltage and temperature (10k minimum write/erase); 100 years typical data retention (15 years minimum)	> Allows EEPROM emulation, reducing system costs and board real estate
The functionality is comp	leted with	Flexible Clock Options	
strong analog capabilitie set of serial modules, a t	s, a complete emperature	Internal clock source module (ICS) containing a frequency-locked loop (FLL) controlled by internal or external reference	> Can eliminate the cost of all external clock components, reduce board space and increase system reliability
sensor and robust memo	ory options.	> Precision trimming of internal reference allows typical 0.1 percent resolution and +0.5 percent to -1 percent deviation over operating temperature and voltage	> Provides one of the most accurate internal clock sources on the market for the money
		> Internal reference can be trimmed from 31.25 kHz to 39.065 kHz, allowing for 8 MHz to 10 MHz FLL output	> Can use trimming to adjust bus clocks for optimal serial communication baud rates and/or timer intervals
HCS08 CPU 4/8 KB Flash On-chip ICE (DBG) BDC		> Low-power oscillator module (XOSC) with software selectable crystal or ceramic resonator range, 31.25 kHz to 38.4 kHz or 1MHz to 16 MHz, and supports external clock source input up to 20 MHz	> 32 kHz oscillator provides low power option for systems requiring time-keeping functionality (i.e., time and date) while in low power modes
2000120100	8-ch., 10-bit	> Outputs 10 mA each: 60 mA max for package	> High-current I/O allows direct drive of LED and other
LVI	ADC SCI	> Outputo to mit output, of mit mar for publicity	circuits to virtually eliminate external drivers and reduce system costs
СОР	SPI	> Software selectable pull-ups on ports when used as input; internal pull-up on RESET and IRQ pin	> Reduces customer system cost by eliminating need for external resistors
liC	2-ch., 16-bit Timer	> Software selectable slew rate control and drive strength on ports when used as output	> Can configure ports for slower slew rate and weaker drive to minimize noise emissions from the MCU

polarity on edge or edge/level modes

> 8-pin keyboard interrupt module with software selectable > Keyboard scan with programmable pull-ups/pull-downs virtually eliminate external glue logic when interfacing to simple keypads



# Ove

HCS08 CPU				
4/8 KB Flash	On-chip ICE (DBG)			
256/512B RAM	BDC			
LVI	8-ch., 10-bit ADC			
COP	SCI			
	SPI			
IIC	2-ch., 16-bit Timer			
Int/Ext Osc.	8-bit Modulo Timer w/ Prescaler			
Internal Clock Source w/ FLL	Up to 13 GPIO			
Temperature Sensor	Analog Comparator			

# Data Sheets

MC9S08QG8

#### Data Sheet for QG8/QG4

# **Cost-Effective Development Tools**

For more information on development tools, please refer to the Freescale Development Tool Selector Guide (SG1011).

#### DEMO9S08QG8 \$50\*

Cost-effective demonstration board with potentiometer, LEDs, serial port and built-in USB-BDM cable for debugging and programming.

## M68CYCLONEPRO \$99\*

HC08/HCS08/HC12/HCS12 stand-alone Flash programmer or in-circuit emulator, debugger, Flash programmer; USB, serial or Ethernet interface options.

# USBMULTILINKBDM \$99\*

Universal HC08 in-circuit debugger and Flash programmer; USB PC interface.

### CWX-H08-SE Free\*\*

CodeWarrior<sup>™</sup> Special Edition for HC(S)08 MCUs; includes integrated development environment (IDE), linker, debugger, unlimited assembler, Processor Expert™ auto-code generator, full-chip simulation and 16 KB C compiler.

\*Prices indicated are MSRP.

\*\*Subject to license agreement and registration.

# **Package Options**

Part Number	Package	Temp. Range			
MC9S08QG4CPAE	8-pin DIP	-40°C to +85°C			
MC9S08QG4CDNE	8-pin SOIC-NB	-40°C to +85°C			
MC9S08QG4CFQE	8-pin DFN	-40°C to +85°C			
MC9S08QG4CDTE	16-pin TSSOP	-40°C to +85°C			
MC9S08QG4CFFE	16-pin QFN	-40°C to +85°C			
MC9S08QG8CDNE	8-pin SOIC-NB	-40°C to +85°C			
MC9S08QG8CFQE	8-pin DFN	-40°C to +85°C			
MC9S08QG8CPBE	16-pin DIP	-40°C to +85°C			
MC9S08QG8CFFE	16-pin QFN	-40°C to +85°C			
MC9S08QG8CDTE	16-pin TSSOP	-40°C to +85°C			
MC9S08QG Family available at -40°C to +125°C in 2H, 2006					

#### Integrated Analog Peripherals

- > 8-channel, 10-bit analog-to-digital converter (ADC)
  - Automatic compare function, software programmable for greater than/equal to or less than conditions
  - Asynchronous clock source
  - Temperature sensor
  - Internal bandgap reference channel
  - Hardware triggerable using the RTI counter
  - Low-power and high-speed options
- > Analog comparator module (ACMP)
- Option to compare to internal reference
- · Option to route comparator output directly to pin
- · Output can be optionally routed to TPM module as input capture trigger

#### **Two Timer Modules**

- > Programmable 16-bit timer/PWM module (TPM)
- > 8-bit modulo timer module (MTIM) with 8-bit prescaler

#### System Protection

- > Watchdog computer operating properly (COP) reset with option to run from dedicated 1 kHz internal clock source or bus clock
- > Low-voltage detection with reset or interrupt
- > Illegal opcode detection with reset
- > Flexible block protection
- > Security feature for Flash and RAM
- > Always-on POR circuitry

Background Debugging System and On-Chip In-Circuit Emulation (ICE) with Real-Time Bus Capture > On-chip in-circuit emulation (ICE) > Provides single wire debugging and emulation interface; eliminates need for expensive emulation tools > Provides circuit emulation without the need for additional, expensive development hardware **Multiple Serial Communication Options** > SCI-serial communications interface module with > All serial peripherals available for use in parallel on

- option for 13-bit break capabilities and double-buffered transmit and receive
- > SPI-serial peripheral interface module
- > I<sup>2</sup>C--inter-integrated circuit bus module

Learn More: For more information about Freescale products, please visit www.freescale.com.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2005

🚰 freescale

> Easy interface to analog inputs, such as sensors

only when result matches condition

such as in STOP3 low-power mode

requires no external components

> Requires only single pin for input signal

comparator with minimal delay

constant measurements

compare level is reached

power requirements

> Used to set conversion complete and generate interrupt

> Calculates temperature without any external components

> Takes periodic measurements without CPU involvement; can be used in STOP3 with compare function to take

measurement and wake MCU from STOP3 only when

> Flexible configuration to meet high performance and low

> Allows other components in system to see results of

> One of the most flexible timer modules for the money; each channel can be independently programmable for input capture, output compare or buffered edge-aligned

> Timer overflow interrupt can be enabled to generate periodic interrupts for time-based software loops

> Resets device in instance of runaway or corrupted code,

and independent clock source provides additional

> Allows system to write/save important variables before

> Can hold device in reset until reliable voltage levels are

> Resets device in instance of runaway or corrupted code

> Secures code sections so that it cannot be accidentally

> Option to put bootloader code in protected space and

> Prevents unauthorized access to memory to protect a

> Significantly reduces risk of code runaway due to

protection in case of loss of clock

voltage drops to low

reapplied to the part

corrupted by runaway code

> Option to protect various block sizes

clear Flash for reprogramming

customer's valuable software IP

brownout situations

16-pin devices

pulse width modulation (PWM) or buffered center-aligned PWM

> Can be used for single slope ADC and RC time

> Can be used to run ADC when MCU clocks are off,

and saves an ADC input channel for other use

> Constant voltage source for calibrating ADC results

These products incorporate SuperFlash® technology licensed from SST.

MC9S08Q684FS REV 0