


Clock Crystal Oscillators Surface Mount Type K50-HC Series



CMOS/ 5.0V/ 7.0×5.0mm

This product is NOT recommended for new designs.



Pb Free

RoHS Conforming

Features

- Miniature ceramic package
- Highly reliable with seam welding
- CMOS output
- Supply voltage $V_{DD}=5.0V$
- $\pm 25ppm$ available

Table 1

Stability Code	Stability (ppm)	T_{OPR} (°C)	Note
0	± 50	-10 to +70 (Standard)	Standard specifications
S	± 30	-10 to +70 (Standard)	With only certain frequencies
U	± 25	-10 to +70 (Standard)	With only certain frequencies
F	± 100	-40 to +85 (Extend)	With only certain frequencies
G	± 50	-40 to +85 (Extend)	With only certain frequencies

How to Order

K50-HC 0 - C S E 25.0000
① ② ③ ④ ⑤ ⑥

- ① Type(7×5 SMD, 5.0V)
- ② Frequency Stability Code(See Table1)
- ③ CMOS Output
- ④ Duty Ratio(S: 45% to 55% STD)
- ⑤ Enable/Disable Function(STD)
- ⑥ Oscillation Frequency(Ex.: 25.0000MHz)

Packaging(Tape & Reel 1Kpcs/reel)


Specifications

Item	Symbol	Conditions	Min.	Max.	Units
Output Frequency Range	F_{OUT}		1.5	68	MHz
Frequency Stability	F_{SBY}	Overall conditions: initial tolerance, operating temperature range, rated power supply voltage change, load change, aging(1year @25°C), shock and vibration	-25 -30 -50	+25 +30 +50	ppm
Storage Temperature Range	T_{STG}		-55	+125	°C
Operating Temperature Range	T_{OPR}	Standard Extend(option)	-10 -40	+70 +85	
Max. Supply Voltage	—		-0.5	7.0	Volt
Supply Voltage	V_{DD}	Stability: $\pm 50ppm, \pm 30ppm, \pm 100ppm$ (Ext Temp) Stability: $\pm 25ppm, \pm 50ppm$ (Ext Temp)	4.5 4.75	5.5 5.25	
Current Consumption (Maximum Loaded)	I_{DD}	$1.5 < F_{OUT} \leq 20MHz$ $20 < F_{OUT} \leq 40MHz$ $40 < F_{OUT} \leq 68MHz$	— — —	25 35 50	mA
Disable Current	I_{DE}	@68.0000MHz	—	30	mA
Duty Ratio(Symmetry)	SYM	@50% V_{DD}	45	55	%
Rise/Fall Time (10% V_{DD} to 90% V_{DD} Maximum Loaded)	T_r/T_f	$8 < F_{OUT} \leq 26MHz$ $26 < F_{OUT} \leq 45MHz$ $45 < F_{OUT} \leq 68MHz$	— — —	10 8 5	nS
Output Voltage-"L"	V_{OL}	$I_{OL}=16mA$	—	10% V_{DD}	Volt
Output Voltage-"H"	V_{OH}	$I_{OH}=-16mA$	90% V_{DD}	—	
Output Load(CMOS)	CL	$8 < F_{OUT} \leq 50MHz$ $50 < F_{OUT} \leq 68MHz$	— —	50 15	pF
Input Voltage Range	V_{IN}		0	V_{DD}	Volt
Input Voltage-"L"	V_{IL}		—	0.8	Volt
Input Voltage-"H"	V_{IH}		2.2	—	
Output Disable Time	—		—	100	nS
Output Enable Time	—		—	100	nS
Start-up Time	ST	@ Minimum operating Voltage to be 0sec.	—	10	mS

Note: Please contact us for inquires about extended operating temperature range, available frequencies and other conditions.
All electrical characteristics are defined at the maximum load and operating temperature range.

Dimensions

(Unit : mm)



Recommended Land Pattern

(Unit : mm)

