


Specifications



Type : Nickel-Metal Hydride Battery			Size : 4/3FA
Capacity ₁₎	Typical		4500mAh
	Minimum		4100mAh
Nominal Voltage			1.2V
Charging Current x Time		Fast Charge ₂₎	3000mA x about 1.6h
Ambient Temp.	Charge Condition	Fast Charge ₂₎	0°C - 40°C
	Discharge Condition		0°C - 50°C
	Storage Condition	- 30days	-20°C - 50°C
		30 - 90days	-20°C - 40°C
		90days - 1year	-20°C - 30°C
Internal Impedance ₃₎ (after discharge to E.V.=1.0V)			About 20mΩ(at 1000Hz)
Weight ₄₎			About 62 g
Size ₄₎ :(Diameter) x (Height)			18.0(D) x 67.5(H) mm

1)Charge : 450mA×16h, Discharge : 900mA(E.V.=1.0V) at 20°C


2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.

Typical Characteristics

Charge



Discharge

