



## SPECIFICATIONS FOR SA301-3400

Output	Voltage	Regulation	Minimum Load	Maximum Load	Peak Load <sup>1</sup>	Ripple P/P (PARD) <sup>3</sup>
V1	+5 V	+ 5%, - 4%	3.0 A	32.0 A	--	50 mV
V2	+12 V	± 5%	0.5 A	12.0 A	15 A	120 mV
V3	-12 V	± 10%	0 A	1.0 A <sup>2</sup>	--	120 mV
V4	-5 V	± 10%	0 A	0.5 A <sup>2</sup>	--	70 mV
V5	-5 VSR	± 10%	0 A	0.1 A	--	--

1. 15 seconds maximum

2. Peak-to-peak with 20 MHz bandwidth and 10  $\mu$ F in parallel with a 0.1  $\mu$ F capacitor.