



Certificate No: RB 28470



PRODUCT INFORMATION

tesa 7158 **Double-sided self-adhesive tape**

Product Description/ Application:

tesa 7158 is a double-sided splicing tape equipped with non-woven backing and coated with an acrylic adhesive of very high tack. It has good shear strength, is resistant to light and ageing, and largely resistant to plasticisers.

Applications:

- Splicing of paper and film webs.
- Mounting of name plates and signs.
- Mounting of plastic bags, continuous stationery, posters, displays etc.

Dimensions:

Lengths:	50, 100 m
Widths:	9, 12, 19, 25, 30, 38, 50, 75, 100 mm

Other dimensions on enquiry.

More sizes than showing

Technical Data: *(mean values)*

Backing	Colour	Liner	Thickness ¹⁾	Adhesive	Adhesion ¹⁾
non-woven fabric	transparent	silicone-coated paper	0,100 mm (without liner)	modified acrylic	16,8 N/25 mm

¹⁾ Parameters of the specification

3582 - 01/95

BDF ●●●●

Beiersdorf UK Ltd

Yeomans Drive, Blakelands, Milton Keynes MK14 5LS

Tel: 01908 211333
Fax: 01908 211555

tesa self adhesive tapes are used successfully in many sectors to solve a variety of problems. Our publications contain numerous examples of such uses, intended to help towards a solution of your particular problems. Each tesa product has been developed for a particular range of applications. Nevertheless, experience has shown that even for one and the same objective, the exact requirements may differ from case to case. We therefore, recommend that you carry out your own tests in each case, to confirm that the tesa self-adhesive tape which you are using is appropriate for your particular use.