
element I 4 Your Electronic Engineering Resource




MCP73213 Dual-Cell Li-Ion Li-Polymer Battery Charge Management Controller

General Description:

The MCP73213 is a dual cell, highly integrated Li-Ion battery charge management controller for use in space-limited and cost-sensitive applications. The MCP73213 can accept an absolute maximum of 18V input and provides a 13V overvoltage protection. The output current can be programmed to be between 130 mA and 1100 mA. The MCP73213 is specified over the ambient temperature range of -40°C to +85°C and is available in a 10 lead, 3x3 mm DFN package.





Legal Disclaimer: The content of the pages of this website is for your general information and use only. It is subject to change without notice. From time to time, this website may also include links to other websites. These links are provided for your convenience to provide further information. They do not signify that we endorse the website(s). We have no responsibility for the content of the linked website(s). Your use of any information or materials on this website meet your own risk, for which we shall not be liable. It shall be your own responsibility to ensure that any products, services or information available through this website meet your specific requirements.

element 4 Your Electronic Engineering Resource

Key Features:

- Complete Linear Charge Management Controller:
 - Integrated Input Overvoltage Protection
 - Integrated Pass Transistor
 - Integrated Current Sense
 - Integrated Reverse Discharge Protection
- Constant Current / Constant Voltage Operation
 with Thermal Regulation
- 4.15V Undervoltage Lockout (UVLO)
- 13V Input Overvoltage Protection
- High Accuracy Preset Voltage Regulation Through Full Temperature Range (-5°C to +55°C):
 - + 0.6%
- Battery Charge Voltage Options:
 - 8.20V, 8.40V, 8.7V or 8.8V
- Resistor Programmable Fast Charge Current:
 - 130 mA 1100 mA
 - Preconditioning of Deeply Depleted Cells:
 - Available Options: 10% or Disable
- Integrated Precondition Timer:
 - 32 Minutes or Disable
- Automatic End-of-Charge Control:
 - Selectable Minimum Current Ratio:
- 5%, 7.5%, 10% or 20%
 - Elapse Safety Timer: 4 HR, 6 HR, 8 HR or
 - Disable
 - Automatic Recharge:
 - Available Options: 95% or Disable
 - Factory Preset Charge Status Output:
 - On/Off or Flashing
 - Soft Start
 - Temperature Range: -40°C to +85°C
 - Packaging: DFN-10 (3 mm x 3 mm)

Application:

- Digital Camcorders
- Portable Media Players
- Ultra Mobile Personal Computers
- Notebook Computers
- Handheld Devices
- Walkie-Talkie

element 4 Your Electronic Engineering Resource

• Low-Cost 2-Cell Li-Ion/Li-Poly Chargers / Cradles

Related Products Information:

Mfr Part #	Farnell #	Newark #	Description
MCP73213-A6SI/MF	1800230	14R8878	Dual Cell Li-Ion/ Li-Polymer Battery Device - DFN
MCP73213-B6SI/MF	1800232	14R8879	Dual Cell Li-Ion/ Li-Polymer Battery Device - DFN

